



Revision Number: 002.1

Issue date: 09/16/2011

1. PRODUCT AND COMPANY IDENTIFICATION

Product name: Dielectric Grease
Product type: Lubricant

IDH number: 270640
Item number: 30536
Region: United States

Company address:
Henkel Corporation
One Henkel Way
Rocky Hill, Connecticut 06067

Contact information:
Telephone: 860.571.5100
Emergency telephone: 860.571.5100
Internet: www.henkelna.com

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

Physical state: Liquid		HEALTH:	1
Color: Clear		FLAMMABILITY:	1
Odor: mild		PHYSICAL HAZARD:	0
		Personal Protection:	See MSDS Section 8
CAUTION: NOT EXPECTED TO PRESENT ANY UNUSUAL HAZARDS IN NORMAL USE. MAY CAUSE SLIGHT EYE, SKIN OR RESPIRATORY TRACT IRRITATION ON REPEATED CONTACT.			

Relevant routes of exposure: Ingestion

Potential Health Effects

Inhalation: When heated to temperatures exceeding 300° F (150° C) in the presence of air, silicones may form formaldehyde vapors. Formaldehyde is a potential cancer hazard and a known skin and respiratory sensitizer. Vapors irritate the eyes, nose and throat. Safe handling conditions may be maintained by keeping formaldehyde vapor concentrations below the OSHA permissible limit. Mist or spray may cause respiratory tract irritation and delayed onset pulmonary edema.

Skin contact: Not expected to be a hazard. Prolonged or repeated contact may cause irritation.

Eye contact: Not expected to cause injury. Eye contact may cause mild irritation.

Ingestion: Not expected under normal conditions of use.

Existing conditions aggravated by exposure: None known

This material is not considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

See Section 11 for additional toxicological information.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous components	CAS NUMBER	%
Dimethyl polysiloxane	63148-62-9	60 - 100
Silica, amorphous, fumed, crystal-free	112945-52-5	5 - 10

4. FIRST AID MEASURES

Inhalation: Move to fresh air. If symptoms develop and persist, get medical attention. If breathing is difficult, give oxygen. Get immediate medical attention.

Skin contact: Wash with soap and water. If symptoms develop and persist, get medical attention.

Eye contact: Get medical attention. Immediately flush eyes with plenty of water for at least 15 minutes. Check for and remove any contact lenses.

Ingestion: Do not induce vomiting. Get medical attention.

5. FIRE FIGHTING MEASURES

Flash point: > 260 °C (> 500°F) HST-US D09F; Flash/Fire Point By Cleveland Open Cup

Autoignition temperature: Not determined

Flammable/Explosive limits - lower: Not available.

Flammable/Explosive limits - upper: Not available.

Extinguishing media: Water spray (fog), foam, dry chemical or carbon dioxide.

Special firefighting procedures: Water should be used to cool closed containers to prevent pressure build-up and possible autoignition or explosion when exposed to extreme heat. Wear a self-contained breathing apparatus with a full face piece operated in pressure-demand or other positive pressure mode.

Unusual fire or explosion hazards: None

Hazardous combustion products: Oxides of carbon.

6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Environmental precautions: Ventilate area. Do not allow product to enter sewer or waterways.

Clean-up methods: Scrape up spilled material and place in a closed container for disposal.

7. HANDLING AND STORAGE

Handling: Avoid contact with eyes, skin and clothing. Use only with adequate ventilation.

Storage: Keep away from heat, spark and flame. Keep in a cool, well ventilated area.

For information on product shelf life contact Henkel Customer Service at (800) 243-4874.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous components	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Dimethyl polysiloxane	None	None	None	None
Silica, amorphous, fumed, crystal-free	10 mg/m3 TWA Inhalable dust. 3 mg/m3 TWA Respirable fraction.	20 MPPCF TWA 0.8 mg/m3 TWA	None	None

Engineering controls: Use local ventilation if general ventilation is insufficient to maintain vapor concentration below established exposure limits.

Respiratory protection: Observe OSHA regulations for respiratory use (29 CFR 1910.134). Use NIOSH approved respirator if there is potential to exceed exposure limit(s).

Eye/face protection: Safety goggles or safety glasses with side shields.

Skin protection:

Chemical resistant, impermeable gloves.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state:	Liquid
Color:	Clear
Odor:	mild
Odor threshold:	Not available.
pH:	Not applicable
Vapor pressure:	< 5 mm hg (77 °F (25°C))
Boiling point/range:	> 300 °F (> 148.9 °C) None
Melting point/ range:	Not available.
Specific gravity:	0.86
Vapor density:	Heavier than air.
Flash point:	> 260 °C (> 500°F) HST-US D09F; Flash/Fire Point By Cleveland Open Cup
Flammable/Explosive limits - lower:	Not available.
Flammable/Explosive limits - upper:	Not available.
Autoignition temperature:	Not determined
Evaporation rate:	Not available.
Solubility in water:	Not available.
Partition coefficient (n-octanol/water):	More soluble in octanol.
VOC content:	0 %; 0 g/l

10. STABILITY AND REACTIVITY

Stability:	Stable
Hazardous reactions:	Will not occur.
Hazardous decomposition products:	Formaldehyde. Oxides of carbon.
Incompatible materials:	Strong acids and strong bases. Strong oxidizing agents.
Conditions to avoid:	Heat, flames, sparks and other sources of ignition.

11. TOXICOLOGICAL INFORMATION

Hazardous components	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Dimethyl polysiloxane	No	No	No
Silica, amorphous, fumed, crystal-free	No	No	No

Hazardous components	Health Effects/Target Organs
Dimethyl polysiloxane	Irritant
Silica, amorphous, fumed, crystal-free	Nuisance dust

12. ECOLOGICAL INFORMATION

Ecological information:	Not available.
--------------------------------	----------------

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Follow all local, state, federal and provincial regulations for disposal.

Hazardous waste number: Not a RCRA hazardous waste.

14. TRANSPORT INFORMATION

U.S. Department of Transportation Ground (49 CFR)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

International Air Transportation (ICAO/IATA)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

Water Transportation (IMO/IMDG)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

15. REGULATORY INFORMATION

United States Regulatory Information

TSCA 8 (b) Inventory Status: All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.
TSCA 12(b) Export Notification: None above reporting de minimus
CERCLA/SARA Section 302 EHS: None above reporting de minimus
CERCLA/SARA Section 311/312: Immediate Health
CERCLA/SARA 313: None above reporting de minimus
California Proposition 65: This product contains a chemical known in the State of California to cause cancer. This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.

Canada Regulatory Information

CEPA DSL/NDL Status: All components are listed on or are exempt from listing on the Canadian Domestic Substances List.
WHMIS hazard class: Not controlled

16. OTHER INFORMATION

This material safety data sheet contains changes from the previous version in sections: New Material Safety Data Sheet format.

Prepared by: Lou Fabrizio, Regulatory Affairs Specialist

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation does not assume responsibility for any results obtained by persons over whose methods Henkel Corporation has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any of Henkel Corporation's products. In light of the foregoing, Henkel Corporation specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation further disclaims any liability for consequential or incidental damages of any kind, including lost profits.