


THIS DRAWING IS A CONTROLLED DOCUMENT
REV 18
8-6828318-3

USED ON



Left Side
Connector(s): LC-Duplex
Mode: MM
Housing Color: Beige
Geom. Spec: N/A

Fiber Path
A - _____ - B
B - _____ - A

Right Side
Connector(s): SC-Duplex
Mode: MM
Housing Color: Beige
Geom. Spec: N/A

- Notes:
- 1 IL tested at 1300nm.
 - 2 Product and Processing must meet requirements of Tyco Electronics Standard 230-702
 - 3 Label 2 will not be present on any cable assembly less than 5 meters long.
 - 4 Includes dust caps (not shown on print).
 - 5 One trace label used on 8-6828318-3, trace label centered on cable assembly

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS, INC. AND ITS AFFILIATES. IT MAY NOT BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC
CE
DIST
16

	B1	Rev Per EC#	MINOR REVISION	2/6/2007	-	JD			
P	LTR	REVISION RECORD		DATE	DN	APVD			

DIMENSIONS: meters	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 P.L.C. ± . 1 P.L.C. ± . 2 P.L.C. ± . 3 P.L.C. ± . 4 P.L.C. ± .

Restricted To:

DNI Cable Assy Configurator		MATERIAL	HEAT TREAT	
CHK	Jeremy Duncan	AMP Tyco Electronics, Inc. Harrisburg, PA 17105-3608		
APVD	Jeremy Duncan			
NAME FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, LC-Duplex to SC-Duplex				
SCALE NTS	SIZE A2	DRAWING NO C- 6828318	SHEET 1 of 3	REV B1

8 7 6 5 4 3 2 1

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT IS NOT TO BE DISCLOSED TO ANY OTHERS AND NO PART OF IT MAY BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA 17105-3608.

THIS DRAWING IS A CONTROLLED DOCUMENT.
PAGE NO

LOC
CE
DIST
16

CAC Customer Layout Rev: D

Part #	L (meters)	L (feet)	LC-Duplex, Beige		SC-Duplex, Beige	
			IL	RL (dB)	IL	RL (dB)
0-6828318-1	0.950 - 1.050	3.11 - 3.44	0.5	-	0.5	-
0-6828318-2	1.950 - 2.050	6.39 - 6.72	0.5	-	0.5	-
0-6828318-3	2.950 - 3.050	9.67 - 10.00	0.5	-	0.5	-
0-6828318-4	3.920 - 4.080	12.86 - 13.38	0.51	-	0.51	-
0-6828318-5	4.920 - 5.080	16.14 - 16.66	0.51	-	0.51	-
0-6828318-6	5.920 - 6.080	19.42 - 19.94	0.51	-	0.51	-
0-6828318-7	6.920 - 7.080	22.70 - 23.22	0.51	-	0.51	-
0-6828318-8	7.920 - 8.080	25.98 - 26.50	0.51	-	0.51	-
0-6828318-9	8.850 - 9.150	29.03 - 30.01	0.51	-	0.51	-
1-6828318-0	9.850 - 10.150	32.31 - 33.30	0.52	-	0.52	-
1-6828318-1	10.850 - 11.150	35.59 - 36.58	0.52	-	0.52	-
1-6828318-2	11.850 - 12.150	38.87 - 39.86	0.52	-	0.52	-
1-6828318-3	12.850 - 13.150	42.15 - 43.14	0.52	-	0.52	-
1-6828318-4	13.850 - 14.150	45.43 - 46.42	0.52	-	0.52	-
1-6828318-5	14.850 - 15.150	48.72 - 49.70	0.52	-	0.52	-
1-6828318-6	15.840 - 16.160	51.96 - 53.01	0.52	-	0.52	-
1-6828318-7	16.830 - 17.170	55.21 - 56.33	0.53	-	0.53	-
1-6828318-8	17.820 - 18.180	58.46 - 59.64	0.53	-	0.53	-
1-6828318-9	18.810 - 19.190	61.71 - 62.95	0.53	-	0.53	-
2-6828318-0	19.800 - 20.200	64.96 - 66.27	0.53	-	0.53	-
2-6828318-1	20.790 - 21.210	68.20 - 69.58	0.53	-	0.53	-
2-6828318-2	21.780 - 22.220	71.45 - 72.90	0.53	-	0.53	-
2-6828318-3	22.770 - 23.230	74.70 - 76.21	0.53	-	0.53	-
2-6828318-4	23.760 - 24.240	77.95 - 79.52	0.54	-	0.54	-
2-6828318-5	24.750 - 25.250	81.20 - 82.84	0.54	-	0.54	-
2-6828318-6	25.740 - 26.260	84.44 - 86.15	0.54	-	0.54	-
2-6828318-7	26.730 - 27.270	87.69 - 89.46	0.54	-	0.54	-
2-6828318-8	27.720 - 28.280	90.94 - 92.78	0.54	-	0.54	-
2-6828318-9	28.710 - 29.290	94.19 - 96.09	0.54	-	0.54	-
3-6828318-0	29.700 - 30.300	97.44 - 99.40	0.55	-	0.55	-
3-6828318-1	30.690 - 31.310	100.68 - 102.72	0.55	-	0.55	-
3-6828318-2	31.680 - 32.320	103.93 - 106.03	0.55	-	0.55	-
3-6828318-3	32.670 - 33.330	107.18 - 109.35	0.55	-	0.55	-
3-6828318-4	33.660 - 34.340	110.43 - 112.66	0.55	-	0.55	-
3-6828318-5	34.650 - 35.350	113.68 - 115.97	0.55	-	0.55	-
3-6828318-6	35.640 - 36.360	116.92 - 119.29	0.55	-	0.55	-
3-6828318-7	36.630 - 37.370	120.17 - 122.60	0.56	-	0.56	-
3-6828318-8	37.620 - 38.380	123.42 - 125.91	0.56	-	0.56	-
3-6828318-9	38.610 - 39.390	126.67 - 129.23	0.56	-	0.56	-
4-6828318-0	39.600 - 40.400	129.92 - 132.54	0.56	-	0.56	-
5-6828318-0	49.500 - 50.500	162.40 - 165.68	0.58	-	0.58	-
8-6828318-0	4.790 - 4.950	15.71 - 16.24	0.51	-	0.51	-

Qty	U of M	Description	Item No.
2	piece	Trace Label	10
2	piece	CONN SUBASSY, MM, SC 1.6MM	9
4	piece	Eyelet/Shrink tube assembly - White	8
2	piece	SC Duplex Clip	7
AR	meter	2 Fiber, XG-50/125, 2.0mm, Twinzip, Aqua, OFNR (Riser)	6
2	piece	2.5mm ferrule cover	5
2	piece	SC Simplex Housing, Beige	4
2	piece	LC Connector Assy, MM	3
1	piece	LC Duplex clip, black	2
4	piece	LC, SC, FC Straight Boot, Beige	1

	B1	Rev Per EC#	MINOR REVISION	2/6/2007	-	JD			
P	LTR	REVISION RECORD			DATE	DIN	APVD		

DIMENSIONS: meters	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 P.L.C. ± - 1 P.L.C. ± - 2 P.L.C. ± - 3 P.L.C. ± - 4 P.L.C. ± -

Restricted To:

DIN Cable Assy Configurator		MATERIAL -	HEAT TREAT -	
CHK Jeremy Duncan				
APVD Jeremy Duncan				
NAME FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, LC-Duplex to SC-Duplex				
SCALE NTS	SIZE A2	DRAWING NO C- 6828318	SHEET 2 of 3	REV B1

8 7 6 5 4 3 2 1

DWG NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

Part #	L (meters)	L (feet)	LC-Duplex, Beige		SC-Duplex, Beige	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
8-6828318-1	7.440 - 7.600	24.40 - 24.93	0.51	-	0.51	-
8-6828318-2	15.088 - 15.392	49.50 - 50.50	0.52	-	0.52	-
8-6828318-3	0.270 - 0.330	0.88 - 1.08	0.5	-	0.5	-

Label 1

Per specification 107-1645-1



Trace # - Bar Code

Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.

Label 2

Per specification 107-1645-1



Trace # - Bar Code

Trace # - Human Readable

Part Number

Country of Origin


This label is used on all lengths on this drawing.

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

B1	Rev Per EC#	MINOR REVISION	2/6/2007	-	JD		
P	LTR	REVISION RECORD	DATE	DIN	APVD		



DIMENSIONS:
meters

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 P.L.C.

1 P.L.C.

2 P.L.C.

3 P.L.C.

4 P.L.C.

±

±

±

±

±

±

±

±

±

±

±

±

±

±

±

±

±

±

±

Restricted To:

DIN	Cable Assy Configurator	MATERIAL	HEAT TREAT
OK	Jeremy Duncan		
APVD	Jeremy Duncan		
NAME	FO C/A - 2 fiber, XG - 50/125, OFNR (Riser) jacket, LC-Duplex to SC-Duplex		
SCALE	SIZE	DRAWING NO	SHEET
NTS	A2	C- 6828318	3 of 3
			REV B1

AMP Tyco Electronics, Inc.
Harrisburg, PA 17105-3608