


- ✓ Closed door panel access
- ✓ Closed door safety
- ✓ Convenient GFCI testing



Maximizes Personnel Protection From:



- Helps protect personnel from Arc Flash hazardous installations covered in NFPA 70E.
- Satisfies control panel utility receptacle standard per NFPA 79*



- ALL utility receptacles must be GFCI protected
- ALL external utility receptacles must be covered
- ALL covers must maintain enclosure rating

* NFPA 79 Electrical Machinery Standard 2002
Edition Sections 16.1.1 (6), 16.1.2

Available in
UL TYPE 4/12 and
UL TYPE 4X Versions!

Hubbell GFCI with
Functionality Indicator

Protective clear cover

Cat 5e Ethernet access

Overcurrent protection



Supplemental "Tool"
entry screw closure


Locking Hasp
accepts 5/32" padlock



Additional
convenience outlet
on GFCI versions

Finger-safe
contacts

Stainless steel
snap latch



NFPA 70E Compliant



Wiring Device-Kellems

Ordering Information

Description	UL TYPE 4/12	UL TYPE 4X
20A 125V GFCI with In-Cabinet Receptacle	 PR20	—
20A 125V GFCI with In-Cabinet Receptacle and Cat 5e Ethernet Access	 PR205E	 PR4X205E
20A 125V GFCI with In-Cabinet Receptacle, Cat 5e Ethernet Access and 3A Circuit Breaker	 PR205EB	 PR4X205EB
Cat 5e Ethernet Access only	 P5E	 P4X5E
15A 125V Power and Cat 5e Ethernet Access	 P155E	 P4X155E
15A 125V Power, Cat 5e Ethernet Access and 3A Circuit Breaker	 P155EB	 P4X155EB

Specifications

Electrical	GFCI - conforms to UL 943 2006 requirement In-Cabinet Receptacle - GFCI protected Data Jack - Cat 5e Circuit Breaker - 3A	Environmental	Enclosure - UL Type 4/12 or UL Type 4X
Mechanical	Cover - Clear Polycarbonate (UV Rated) Housing - Cast Aluminum Finish - Powder Coat Latch - Stainless steel	Certification	UL Recognized CSA Certified

