




HONEYWELL PART NUMBER
V15H16-CZ300A05-K
PRODUCT CODE
CFW2066

REV	DOCUMENT	CHANGED BY	CHECK
A	0038670	VS 10APR08	BLR



NOTES:

1. TERMINALS WILL ACCEPT 6.35mm WIDE QUICK CONNECT RECEPTACLES AND COMPLY WITH EN61058-1 REQUIREMENTS.

CHARACTERISTICS		ELECTRICAL DATA		DESIGN UNITS: MM			DRAWN	KSR	01APR08	Honeywell									
		CONTACT ARRANGEMENT S.P.D.T		TOLERANCES UNLESS NOTED:			CHECK	RJ	01APR08										
OPERATING FORCE: 350gf MAX.		 16(4)A 250V~ 25T150 μ 5E4		NO PLACE X ± ±			THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - BASIC									
DIFFERENTIAL FORCE:				ONE PLACE .X ± ±															
RELEASE FORCE: 60gf MIN.				TWO PLACE .XX ± ± ± 0.40															
FREE POSITION:				THREE PLACE .XXX ± ±															
OPERATING POSITION: 20.6±0.8MM.				 16A 1/2HP 125/250VAC		ANGLES X ± ± ± 2°			INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE B	TYPE I	CAGE CODE		DRAWING NAME V15H16-CZ300A05-K		REV A	
PRE-TRAVEL: 1.6MM MAX.		THIRD ANGLE PROJECTION 				AutoCAD			SCALE	NTS				SHEET		1	OF	1	
DIFFERENTIAL TRAVEL: 0.4MM MAX.																			
OVER-TRAVEL: 0.8MM MIN.																			
FULL OVERTRAVEL FORCE:																			