






MOD		LOC	DIST	P		ZONE	LTR	REVISIONS		DATE	APPD
1	8	GP	00					A1	REV PER ECO-09-023313	13OCT09	AEG
								A	REV PER EC OS13-0177-03	5-03	CR



RECOMMENDED PANEL CUT-OUT

- 1. SHELL: BRASS; CONTACTS: PHOSPHOR BRONZE; HOUSING: POLYESTER, UL 94V-0 RATED, BLACK.
- 2. 0.76 μm [.000030] MIN GOLD ON MATING END FOR A LENGTH OF 1.37[.054] MIN ON INSIDE, 2.54 μm [.000100] MIN TIN-LEAD FOR A LENGTH OF 3.30[.130] MIN FROM OPPOSITE END, ALL OVER 1.27 μm [.000050] MIN NICKEL.
- 3. 0.38 μm [.000015] MIN GOLD ON MATING END FOR A LENGTH OF 1.37[.054] MIN ON INSIDE, 2.54 μm [.000100] MIN TIN-LEAD FOR A LENGTH OF 3.30[.130] MIN FROM OPPOSITE END, ALL OVER 1.27 μm [.000050] MIN NICKEL.
- 4. 2.54 μm [.000100] MIN TIN-LEAD OVER 1.27 μm [.000050] MIN NICKEL.
- 5. GOLD PLATING PER MIL-G-45204, TIN PLATING PER MIL-T-10727, NICKEL PLATING PER QQ-N-290.
- 6. RECEPTACLE ASSEMBLY MATES WITH 4 PIN, 8.99 $\pm$ 0.10[.354 $\pm$.004] DIAMETER PLUG.
- 7. 2.54 μm [.000100] MIN TIN OVER 1.27 μm [.000050] MIN NICKEL.
- 8. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED PC BOARD LAYOUT
BOTTOM VIEW

OBSOLETE 8	7	2	3	-750315-4-
	4	5	2	-750315-3-
	4	5	3	750315-2
	4	5	3	750315-1
INNER SHELL FINISH		CONTACT FINISH		PART NO

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC $\pm$ 0.13[.005] 3 PLC DEC $\pm$ - ANGLES $\pm$ - MATERIAL $\triangle$ FINISH SEE TABLE		DR 8-6-90 R.SHIREY CHK - APPD - PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		NAME RECEPTACLE ASSEMBLY, 4 POSN, LOW FLANGE, UNSHIELDED, VERTICAL, MINIATURE CIRCULAR DIN	
SIZE D		CAGE CODE 00779		DRAWING NO 750315	
SCALE 5:1		SHEET 1 OF 1			

METRIC