




FCI P/N (NOTE 1)	"L" (NOTE 1)
57850-XXXX	XXX



NOTES:
1. FCI P/N = DRAWING NO. A DASH AND A SUFFIX XXXX
WHERE Y-M IS METERS AND Y-F IS FEET AND XXX IS
UNIT OF LENGTH "L".
E.G. 57850-M004 IS 4 METERS IN LENGTH.

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		title		code	
lit	ech no	dr	date	linear	NOMINALS ONLY	projection	copy	size	ding no	sheet	1 of 1
A	V1330	JUK	5/24/01		UNLESS NOTED			A4	57650	213	
				angles							
				dr	J. KULE 5/24/01						
				engr	G. WARNER 5/24/01						
				chr	G. WARNER 5/24/01						
				appr	G. WARNER 5/24/01						
sheet	revision	A									
index	sheet	1									

SPECIFICATIONS	
LC	SC
INSERTION LOSS	0.25dB MAX 0.5dB MAX
RETURN LOSS	55dB MIN 50dB MIN
FIBER PROTRUSION	50mm MAX 50mm MAX
APEX OFFSET	45um MAX 45um MAX
FIBER UNDERCUT	SEE TELECORDIA GR-326