

Brilliance by design


LED Replacement for Incandescent Lamps

MODEL 513

T-1 3/4 Wedge base LED is available in all colors. Direct replacement for T-1 3/4 wedge base incandescent lamps.

FEATURES

- Available in all colors and voltages
- Long life LEDs
- Low power consumption
- Direct replacement for: 11*, 17, 18, 37, 56, 73, 74, 79, 84, 85 & 86



HOW TO ORDER

NOTE:

* External resistor required

*For voltage/current specs, see page 7-9

Voltage

2.5vdc

5vdc

6.3vdc

14vdc

28vdc

Model No.

513-205X*

513-5X

513-603X


513-14X

513-28X

Where the 'X' appears insert: 1-Red, 2-Green, 3-Yellow, 4-Amber, 5-Ultra Green, 6-Ultra Blue, 7-Pure White

MODEL 516

T-3 1/4 Bi-pin LED is available in all colors. Direct replacement for the T-3 1/4 wedge base bi-pin incandescent lamps. Unit available in both standard 160 degree viewing angle for switches and wide viewing applications and 30 degree for narrow viewing surfaces that require extra brightness. Please specify when ordering. For example: 516-127D for 12vdc white LED for narrow ultra bright illumination or 516-127 for 12vdc white LED for wide bright illumination.



513 516

FEATURES

- Available in all colors and voltages
- Long life LEDs
- Low power consumption
- Direct replacement for: 124, 147, 152, 158, 159, 161, 168, 184, 190, 192-194, 259, 280, 285, 400, 444, 447, 464, 555, 585, 655, 656, 657, 658, 740, 758, 947, 3-501, 3-504, 3-505, 3-507

HOW TO ORDER

Voltage

5vdc

6vdc

7vdc

12vdc

14vdc

24vdc

28vdc

Model No.

516-5X

516-6X

516-7X

516-12X

516-14X

516-24X

516-28X

Where the 'X' appears insert: 1-Red, 2-Green, 3-Yellow, 4-Amber, 5-Ultra Green, 6-Ultra Blue, 7-Pure White

NOTE:

*For voltage/current specs, see page 7-9

Brilliance by design

LED Replacements for Incandescent Lamps

LED Specifications and Technical Data

LED data for models 160, 162, 164, 460, 510, 516, 522, 532, 513, 541

Color Choice	LED Size	Raw Chip Material	Emitted Color	Wave Length	Viewing Angle (Deg.)	Iv (mcd) Typical	If (mA) Typical	Vf (V) Typical
1	T 1-3/4	GaAlAs	Red	660	22	3000-4000	20	2.1
2	T 1-3/4	Gap	Green	565	20	750	20	1.8
3	T 1-3/4	AlInGap	Yellow	595	22	2000-3000	25	2.1
4	T 1-3/4	AlInGap	Amber	611	22	2000-3000	25	2.1
5	T 1-3/4	InGaN	Ultra Green	575	30	2200	25	3.5
6	T 1-3/4	InGaN	Blue	470	30	500	25	3.5
7	T 1-3/4	InGaN/ YAG	Pure White		45	1200	25	3.5

LED data for models 159, 197, 311

Color Choice	LED Size	Raw Chip Material	Emitted Color	Wave Length	Viewing Angle (Deg.)	Iv (mcd) Typical	If (mA) Typical	Vf (V) Typical
1	T-1	GaAlAs	Red	660	30	1250	20	1.8
2	T-1	Gap	Green	568	20	500	20	1.8
3	T-1	AlInGap	Yellow	595	30	500	25	2.1
4	T-1	AlInGap	Amber	611	30	500	25	2.1
5	T-1	InGaN	Ultra Green	575	30	1700	25	3.5
6	T-1	InGaN	Blue	470	30	650	25	3.5
7	T-1	InGaN/ YAG	Pure White		45	630	25	3.5

Note: The specifications listed above are subject to change. For special LED requirements and color please contact SloanLED.