







TOLERANCES
UNLESS OTHERWISE SPECIFIED: ±0.3

CAT. NO.	NO. OF CONTACTS (MATING SIDE)	DIMENSIONS				
		A	B	C	D	E
PHEC30P-S21L	15/ROW X 2 ROWS	34.55	31.75	30.3	20.42	17.78
PHEC34P-S21L	17/ROW X 2 ROWS	37.09	34.29	32.84	22.96	20.32
PHEC40P-S21L	20/ROW X 2 ROWS	40.9	38.1	36.65	26.77	24.13
PHEC50P-S21L	25/ROW X 2 ROWS	47.25	44.45	43	33.12	30.48
PHEC60P-S21L	30/ROW X 2 ROWS	53.6	50.8	49.35	39.47	36.83
PHEC68P-S21L	34/ROW X 2 ROWS	58.68	55.88	54.43	44.55	41.91
PHEC80P-S21L	40/ROW X 2 ROWS	66.3	63.5	62.05	52.17	49.53
PHEC100P-S21L	50/ROW X 2 ROWS	79.0	76.2	74.75	64.87	62.23
PHEC120P-S21L	60/ROW X 2 ROWS	91.7	88.9	87.45	77.57	74.93

MATERIAL

INSULATOR: NYLON RESIN GLASS REINFORCED (UL94V-0)

COLOR: BLACK

CONTACT: COPPER ALLOY

MOUNTING LATCH: PHOSPHOR BRONZE

SOLDER PLATED

CONTACT PLATING TABLE

CONTACT AREA	REMAINDER
GOLD 0.25 MIN	SOLDER
OVER NICKEL 3Z	OVER NICKEL

PRINTED CIRCUIT CONNECTOR

CAT. NO. PHEC__P-S21L

DRAWING NO. JSC 90735

REV 3

BURNDY
JAPAN, Ltd.

DESIGNED

DRAWN

CHECKED

APPROVED

DATE

M. Oba

4.8/1

J. Toyoshima

Mar. 8, 1990

SCALE

DIM IN

MATERIAL


mm

REV	DATE	DESCRIPTION	CHK
1	8-11 '92	30,34,50,68 POSITIONS ADDED.	JSC
2	6-5 '90	EC 7866	JSC
1	4-20 '90	EC 7837	JSC



REFERENCE

10-PHEC 02

DRAWING NO
JSC 90735




PHEC...R-S211




PHEC...R-S210

RECOMMENDED PC BOARD
THICKNESS: 1.6 ± 0.2
HOLE PATTERN (COMPONENT SIDE)
NO. OF CONTACTS: 40, 60, 80, 100, 120
N: NO. OF CONTACTS




NO. OF CONTACTS: 30, 34, 50

NOTE
THROUGH-HOLES FOR MOUNTING LATCHES ALSO SHOULD
BE PLATED.




TOLERANCES
UNLESS OTHERWISE SPECIFIED: ±0.3

NO. OF CONTACTS: 40, 60, 80, 100, 120



CRITERION PIN

NO. OF CONTACTS: 30, 34, 50



MATERIAL

INSULATOR: PBT RESIN GLASS REINFORCED (UL94V-0)

COLOR: BLACK

CONTACT: PHOSPHOR BRONZE

MOUNTING LATCH: PHOSPHOR BRONZE
SOLDER PLATED

CONTACT PLATING TABLE

(THICKNESS: μm)

CONTACT AREA	REMAINDER
GOLD 0.25 MIN. OVER NICKEL 3.2	SOLDER OVER NICKEL

PRINTED CIRCUIT CONNECTOR

CAT. NO.

PHEC...R-S211

DRAWING NO.

JSC 90737

BURNDY
JAPAN, Ltd.

DESIGNED

DRAWN

CHECKED

APPROVED

DATE

M. Oba

A. Ebi

T. Koyama

Mar. 8, 1990

SCALE

DIM. IN

MATERIAL

mm

93
1-29 WRONG CONTACT DIM. CORRECTED.




92
3 8-11 30, 34, 50, 68 POSITIONS ADDED No. 5.9

90
2 5-30 EC 7866 No. JK


90
1 4-20 EC 7837 No. JK

REV. DATE DESCRIPTION CKD


REFERENCE




RECOMMENDED P.C. BOARD
THICKNESS : 1.6 ±0.2
HOLE PATTERN (COMPONENT SIDE)



NOTE
PROVIDE LAND SO THAT FLANGE PORTION OF THE CONNECTOR
CAN BE PUT.



TOLERANCES
UNLESS OTHERWISE SPECIFIED : ±0.3



PHEC60RT-S212

MATERIAL

INSULATOR : PPS RESIN GLASS REINFORCED (UL94V-0)
COLOR : BLACK

CONTACT : PHOSPHOR BRONZE

SCREW NUT : STAINLESS

NO. OF CONTACTS : 30/ROW X 2 ROWS (MATING SIDE)

CONTACT PLATING TABLE

CONTACT AREA		REMAINDER	
GOLD 0.25 MIN.		SOLDER	
OVER NICKEL 32		OVER NICKEL	







PRINTED CIRCUIT CONNECTOR
SURFACE MOUNT TYPE

REV	DATE	DESCRIPTION	CHKD.
4	8-14 '92	WRONG CONTACT DIM. CORRECTED	
3	1-8 '92	100 POSITIONS OF DELETED.	
2	6-8 '90	DIM. CHANGED.	
1	4-20 '90	EC7866	
		VARIATION ADDED.	

SCALE
DIM. IN
MATERIAL

DESIGNED
DRAWN
CHECKED
APPROVED
DATE

CAT. NO.
PHEC60RT-S21_
DRAWING NO.
JSC 90739
REV
4
BURNDY
JAPAN, Ltd.



RECOMMENDED PC BOARD
THICKNESS: 1.6 ± 0.2
HOLE PATTERN (COMPONENT SIDE)

LAND PROVIDING AREA

NOTE

TOLERANCES
UNLESS OTHERWISE SPECIFIED: ±0.3

MATERIAL

INSULATOR : PPS RESIN GLASS REINFORCED (UL94V-0)
COLOR : BLACK

CONTACT : PHOSPHOR BRONZE

SCREW NUT : STAINLESS

NO. OF CONTACTS : 50/ROW X 2 ROWS (MATING SIDE)

CONTACT PLATING TABLE

[THICKNESS : μm]

CONTACT AREA	REMAINDER
GOLD 0.25 MIN. OVER NICKEL 3Z OVER NICKEL	SOLDER

PRINTED CIRCUIT CONNECTOR
SURFACE MOUNT TYPE

CAT. NO.	PHEC100RT-S21
DRAWING NO.	JSC 91839
REV	0

BURNDY
JAPAN, Ltd.

DESIGNED
DRAWN
CHECKED
APPROVED
DATE Aug. 11, 1992

SCALE
DIM. IN
MATERIAL

REV	DATE	DESCRIPTION	CHKD.

DRAWING NO.
JSC 90752

MATERIAL
INSULATOR : PBT RESIN GLASS REINFORCED (UL94V-0)
COLOR : BLACK
CONTACT : PHOSPHOR BRONZE
MOUNTING LATCH : PHOSPHOR BRONZE
SOLDER PLATED

CONTACT PLATING TABLE
[THICKNESS, μ m]



CONTACT AREA	REMAINDER
GOLD 0.25 MIN OVER NICKEL 3.2	SOLDER OVER NICKEL

REV	DATE	DESCRIPTION	CHKD.
5	'93 6-22	100 POSITIONS ADDED.	M.O.
4	'93 2-1	WRONG CONTACT DIM. CORRECTED.	M.O.
3	'92 8-11	100,120 POSITIONS DELETED. 30,34,50,68 POSITIONS ADDED.	M.O.
2	'90 5-30	DIM. CHANGED (36.61 $\rightarrow$ 33.61)	M.O.
1	'90 5-14	EC 7866	HE

REFERENCE

CAT. NO.	NO. OF CONTACTS (MATING SIDE)	DIMENSIONS				
		A	B	C	D	E
PHEC30R-S21-H	15/ROW X 2 ROWS	34.55	31.75	27.26	21.26	17.78
PHEC34R-S21-H	17/ROW X 2 ROWS	37.09	34.29	29.8	23.8	20.32
PHEC40R-S21-H	20/ROW X 2 ROWS	40.9	38.1	33.61	27.61	24.13
PHEC50R-S21-H	25/ROW X 2 ROWS	47.25	44.45	39.96	33.96	30.48
PHEC60R-S21-H	30/ROW X 2 ROWS	53.6	50.8	46.31	40.31	36.83
PHEC68R-S21-H	34/ROW X 2 ROWS	58.68	55.88	51.39	45.39	41.91
PHEC80R-S21-H	40/ROW X 2 ROWS	66.3	63.5	59.01	53.01	49.53
PHEC100R-S21-H	50/ROW X 2 ROWS	79.0	76.2	71.71	65.71	62.23

TOLERANCES
UNLESS OTHERWISE SPECIFIED: ± 0.3






SCALE	DESIGNED	CAT. NO.
DIM. IN mm	DRAWN	PHEC_R-S21-H
MATERIAL	CHECKED	DRAWING NO.
	APPROVED	REV
	DATE	

PRINTED CIRCUIT CONNECTOR
HIGH STAND OFF TYPE


BURNDY
JAPAN, Ltd.

RECOMMENDED PC BOARD
THICKNESS: 1.6 ±0.2
HOLE PATTERN (COMPONENT SIDE)


NO. OF CONTACTS: 40,60,68




NO. OF CONTACTS: 30,34,50



NO. OF CONTACTS: 40,60,68



NO. OF CONTACTS: 30,34,50



CAT. NO.	NO. OF CONTACTS (MATING SIDE)	DIMENSIONS				
		A	B	C	D	E
PHEC30R-S21-H1	15/ROW X 2 ROWS	34.55	31.75	27.26	21.26	17.78
PHEC34R-S21-H1	17/ROW X 2 ROWS	37.09	34.29	29.8	23.8	20.32
PHEC40R-S21-H1	20/ROW X 2 ROWS	40.9	38.1	33.61	27.61	24.13
PHEC50R-S21-H1	25/ROW X 2 ROWS	47.25	44.45	39.96	33.96	30.48
PHEC60R-S21-H1	30/ROW X 2 ROWS	53.6	50.8	46.31	40.31	36.83
PHEC68R-S21-H1	34/ROW X 2 ROWS	58.68	55.88	51.39	45.39	41.91

TOLERANCES
UNLESS OTHERWISE SPECIFIED: ±0.3

MATERIAL

INSULATOR: PBT RESIN GLASS REINFORCED (UL94V-0)

COLOR: BLACK

CONTACT: PHOSPHOR BRONZE

MOUNTING LATCH: PHOSPHOR BRONZE

SOLDER PLATED

CONTACT PLATING TABLE

[THICKNESS: μm]

CONTACT AREA	REMAINDER
GOLD 0.25 MIN. OVER NICKEL 3.2	SOLDER OVER NICKEL

PRINTED CIRCUIT CONNECTOR
HIGH STAND OFF TYPE
CAT. NO.

PHEC_R-S21-H1

DRAWING NO. REV

JSC 91840 1

BURNDY
JAPAN, Ltd.

DESIGNED
DRAWN *M. Oba*
CHECKED A.matsuo
APPROVED *S. Ito*
DATE Aug. 17, 1992

SCALE
DIM IN mm
MATERIAL

1 93
2-1 WRONG CONTACT DIM. CORRECTED.

REV DATE DESCRIPTION CKD

REFERENCE

DRAWING NO. JSC 91840

