



PART NO.	ENG. NO.	
02-06-1101	1561-(P901)	
02-06-1103	1561-(P901)L	
02-06-5101	1561-(P561)	
02-06-5102	1561-(P561)L	
02-06-5108	1561-(P228)	
02-06-5109	1561-(P228)L	
02-06-5100	1561-(P550)	
02-06-5103	1561-(P550)L	
02-06-5105	1561-(P591)	
02-06-5104	1561-(P591)L	
02-06-1118	1561-1(P901)	
NOT TOOLED	1561-1(P901)L	



LEGEND


1561-*(****)*

BLANK=WITH LOCKING TABS
1=WITHOUT LOCKING TABS


P=PREPLATE
BLANK=POSTPLATE

FORM
BLANK=CHAIN
L=LOOSE

FINISH CODE




(.25)
.010
MAX.
CARRIER CUTOFF




(.25)
.010
MAX.
CARRIER CUTOFF

(1.50/1.42)
.059/.056
DIA.



SELECT GOLD
PLATE DEPTH
(WHEN SPECIFIED)



CARRIER VIEW
ACTUAL SIZE

(2.03)
.080

(1.52)
.060
(.38)
.015

SECT. "A-A"

NOTES:

- MATERIAL: BRASS
- FINISH:
 - HOT TIN DIP (.00051)/.000020 MIN.
 - SELECT GOLD PLATE (.00075)/.000030 MIN. IN CONTACT AREA, SELECT TIN, (.00250)/.000100 MIN. IN CRIMP AREA OVER (.00125)/.000050 MIN. NICKEL OVERALL.
 - SELECT GOLD PLATE (.00076)/.000030 MIN. IN CONTACT AREA, OVER (.00127)/.000050 MIN. NICKEL OVERALL.
 - SELECT GOLD PLATE (.00175)/.000050 MIN. IN CONTACT AREA, OVER (.00127)/.000050 MIN. NICKEL OVERALL WITH (.000025)/.000010 MAX. GOLD FLASH OVERALL.
 - SELECT GOLD PLATE (.00038)/.000015 MIN. IN CONTACT AREA, OVER (.00076)/.000030 MIN. NICKEL OVERALL WITH (.000025)/.000010 MAX. GOLD FLASH OVERALL.
- PRODUCT SPECIFICATION: PS-02-06.
- PACKAGING INFORMATION: NOT AVAILABLE
- TERMINAL FOR USE WITH (1.57)/.062 DIA. SERIES HOUSINGS AND WILL ACCEPT 18 THRU 24 AWG WIRE WITH (1.52/3.05)/.060/.120 INSULATION DIA.
- PARTS CONFORM TO CLASS B REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.

CORRECT TOLERANCE	
EC NO: UCP2015-0937	2014/09/02
DRWN:KIPPER	2014/09/02
CHKD:NGUYEN	2014/09/02
APPR:FSMITH	2014/09/04
REV	
AP1	

QUALITY SYMBOLS
▽=0
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)	
mm	INCH
4 PLACES ± ---	± ---
3 PLACES ± ---	± .010
2 PLACES ± 0.25	± .014
1 PLACE ± 0.36	± ---
0 PLACE ±	±
ANGULAR ±1/2°	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

DIMENSION STYLE MM/IN	
DRAWN BY	DATE
GEW	1991/02/19
CHECKED BY	DATE
RW	1991/02/19
APPROVED BY	DATE
GW	1991/02/19
MATERIAL NO.	
SEE CHART	
SIZE	
C	

SCALE 6:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION
TITLE		
CRIMP TERMINAL, FEMALE .062 DIA. FOR 18-24 AWG WIRE		
molex		
DOCUMENT NO. SD-1561-*		SHEET NO. 1 OF 1
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		