






FCIconnect.com B

Copyright FCI



mat'l. code -				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family RIBCAGE				
ltr ecn no dr date				tolerances unless otherwise specified				 INCH/MM scale 4:1		title RIBCAGE III T/M VERT. HEADER ASS'Y				
L J10329		CRG	6/6/01		angles		linear							
M M05-0123		MHT	6/6/05											
N M06-0225		ERE	06/12/06		0'±2'									
P M06-0370		MHT	9/26/06		dr	M. CORNMAN		6/6/95		dwg no sheet 1 of 6 95776 A3				
R M09-0058		MHT	4/04/09		engr	D. WHITING		6/6/95						
S N10-0122		YO	5/10/10		chr	D. WHITING		6/6/95						
T ELX-N-009749		YO	1/31/12		appd	D. WHITING		6/6/95						
sheet index		revision sheet		T	T	T	T	T	T					
				1	2	3	4	5	6					




FCIconnect.com


Copyright FCI

PRODUCT NUMBER
SEE TABLE

SIZE	DIM H	DIM J	DIM K	DIM L
2X5	.275/6.99	.200/5.08	.372/9.45	.320/8.13
2X10	.525/13.34	.450/11.43	.622/15.80	.570/14.48
2X15	.775/19.68	.700/17.78	.872/22.15	.820/20.83
2X20	1.025/26.03	.950/24.13	1.122/28.50	1.070/27.18
2X25	1.275/32.38	1.200/30.48	1.372/34.85	1.320/33.53
2X30	1.525/38.74	1.450/36.83	1.622/41.20	1.570/39.88
2X35	1.775/45.08	1.700/43.18	1.872/47.55	1.820/46.23
2X40	2.025/51.43	1.950/49.53	2.122/53.90	2.070/52.58
2X45	2.275/57.78	2.200/55.88	2.372/60.25	2.320/58.93
2X50	2.525/64.14	2.450/62.23	2.622/66.60	2.570/65.28



SECTION X-X
ROTATED 90° CW




SECTION Y-Y

mat'l. code -				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family RIBCAGE			
ltr	ecn	no	dr	date	tolerances unless otherwise specified		scale 4:1	title		
T					angles	linear		RIBCAGE III T/M		
					0.002	.XXX±.005/0.13		VERT. HEADER ASS'Y		
						.XXX±.0020/0.051				
					dr	M. CORNMAN	6/6/95	dwg no		sheet 2 of 6
					enr	D. WHITING	6/6/95	95776		A3
					chr	D. WHITING	6/6/95			
					appd	D. WHITING	6/6/95	type Product Customer Drawing		
sheet index	revision sheet									


PRODUCT NUMBER
SEE TABLE

LOCATOR/HOLDDOWN VARIATIONS

STYLE
1




STYLE
2





(ALL PEG CONFIGURATIONS)


STYLE
4



STYLE
6



STYLE
7




mat'l. code -				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family RIBCAGE			
ltr	ecn	no	dr	date	tolerances unless otherwise specified					title			
T					angles	linear	.XX±.01/0.3		INCH/MM ↔	RIBCAGE III T/M VERT. HEADER ASS'Y			
							.XXX±.005/0.13						
				0氣2?	.XXXX±.0020/0.051								
					dr	M. CORNMAN	6/6/95			dwg no		sheet3 of 6	size
					engr	D. WHITING	6/6/95			95776		A3	
					chr	D. WHITING	6/6/95						
					appd	D. WHITING	6/6/95			type Product Customer Drawing			
sheet index		revision sheet											


PRODUCT NUMBER
SEE TABLE

RECOMMENDED P. C. B. LAYOUT


STYLE
1




STYLE
6




STYLE
2



STYLE
7



STYLE
4




mat'l. code				surface	tolerance	projection	product family		
-				ISO 1302 ✓	ISO 406 ISO 1101	ISO 406 ISO 1101	RIBCAGE		
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title		
T					angles	linear	RIBCAGE III T/M		
					0.002?		VERT. HEADER ASS'Y		
							dwg no		
					dr	M. CORNMAN	6/6/95	sheet 4 of 6	size
					enr	D. WHITING	6/6/95	95776	A3
					chr	D. WHITING	6/6/95	type	
					appd	D. WHITING	6/6/95	Product Customer Drawing	
sheet	revision								
index	sheet								


PRODUCT NUMBER
SEE TABLE

RECOMMENDED P. C. B. LAYOUT


STYLE
1




STYLE
2



STYLE
4



STYLE
6



mat'l. code				surface	tolerance	projection	product family
-				ISO 1302 ☒	ISO 406 ISO 1101		RIBCAGE
ltr	ecn	no	dr	date	tolerances unless otherwise specified	INCH/MM	title
T					angles	☒	RIBCAGE III T/M
					linear	☒	VERT. HEADER ASS'Y
					0.002?	☒	dwg no
					dr M. CORNMANN	6/6/95	sheet 5 of 6
					enrg D. WHITING	6/6/95	size
					chr D. WHITING	6/6/95	95776
					appd D. WHITING	6/6/95	A3
sheet index				revision	sheet	type Product Customer Drawing	

