

D5SC4MR

40V 5A


FEATURES

- Tj150°C
- PRRSM avalanche guaranteed
- Fully Isolated Molding

APPLICATION

- Switching power supply
- DC/DC converter
- Home Appliances, Office Equipment
- Telecommunication

OUTLINE DIMENSIONS



RATINGS

● Absolute Maximum Ratings (If not specified Tc=25°C)


Item	Symbol	Conditions	Ratings	Unit
Storage Temperature	Tstg		-40~150	°C
Operating Junction Temperature	Tj		150	°C
Maximum Reverse Voltage	VRM		40	V
Repetitive Peak Surge Reverse Voltage	VRSM	Pulse width 0.5ms, duty 1/40	45	V
Average Rectified Forward Current	IO	50Hz sine wave, R-load, Rating for each diode Io/2, Tc=136°C	5	A
Peak Surge Forward Current	IFSM	50Hz sine wave, Non-repetitive 1 cycle peak value, Tj=125°C	50	A
Repetitive Peak Surge Reverse Power	PRSM	Pulse width 10 μs, Rating of per diode, Tj=25°C	330	W
Dielectric Strength	Vdis	Terminals to case, AC 1 minute	1.5	kV
Mounting Torque	TOR	(Recommended torque: 0.3N·m)	0.5	N·m

● Electrical Characteristics (If not specified Tc=25°C)


Item	Symbol	Conditions	Ratings	Unit
Forward Voltage	VF	IF=2.5A, Pulse measurement, Rating of per diode	Max 0.55	V
Reverse Current	IR	VR=VRM, Pulse measurement, Rating of per diode	Max 2.5	mA
Junction Capacitance	Cj	f=1MHz, VR=10V, Rating of per diode	Typ 116	pF
Thermal Resistance	θjc	junction to case	Max 3.3	°C/W
	θjf	junction to heatsink (Reference value)	Max 4.8	

D5SC4MR

Forward Voltage




D5SC4MR Junction Capacitance




D5SC4MR

Reverse Current




D5SC4MR Reverse Power Dissipation



$T_j = 150^\circ\text{C}$



D5SC4MR Forward Power Dissipation




$T_J = 150^\circ\text{C}$




D5SC4MR


Derating Curve



$V_R = 20V$



D5SC4MR Peak Surge Forward Capability



SBD Repetitive Surge Reverse Power Derating Curve

