




Sensing distance			Supply voltage	Output
20 mm		5 mm	12 to 24 VDC	 100/200 mA NPN or PNP
1.5 mm		3 mm		
3 mm		5 mm		

Inductive Proximity Sensor

TL-W/WM

Space Saving Flat Proximity Switch

- Space-saving, low-profile rigid aluminum die-cast housing (TL-W5E/F).
- All models provided with an operation indicator.
- Mounting possible from either the front or rear of the housing.
- Protected to endure water and oil splashes (conforms to IEC IP67).
- DC 2-wire models (TL-W5MD1/-W5MD2) provide easy wiring.



Ordering Information

DC 2-wire


Sensing head	Sensing distance	Output			
		NPN		PNP	
		NO	NC	NO	NC
Non-shielded	5 mm	TL-W5MD1	TL-W5MD2	---	---

DC 3-wire

Sensing head	Sensing distance	Output			
		NPN		PNP	
		NO	NC	NO	NC
Shielded	5 mm	TL-W5E1	TL-W5E2	TL-W5F1	TL-W5F2
Non-shielded	1.5 mm	TL-W1R5MC1	---	TL-W1R5MB1	---
	3 mm	TL-W3MC1	TL-W3MC2	TL-W3MB1	TL-W3MB2
	5 mm	TL-W5MC1	TL-W5MC2	TL-W5MB1	---
	20 mm	TL-W20ME1	TL-W20ME2	---	---

Application Examples

Position of Workpiece



Specifications

■ Ratings/Characteristics

DC 2-wire

Item		TL-W5MD
Sensing distance		5 mm ±10%
Supply voltage (operating voltage range)		12 to 24 VDC (10 to 30 VDC)
Current consumption (leakage current)		0.8 mA max.
Sensing object		Magnetic metals (refer to “ <i>Engineering Data</i> ” for non-magnetic metals)
Setting distance (standard sensing object)		0 to 4 mm (iron, 18 x 18 x 1 mm)
Differential travel		10% max. of sensing distance
Response frequency (see note)		0.5 kHz
Operating mode (for detecting sensing objects)		D1 models: Load ON D2 models: Load OFF
Control output (switching capacity)		3 to 100 mA DC
Circuit protection		Load short-circuit protection
Indicator		D1 models: Operation indicator (red LED), operation set indicator (green LED) D2 models: Operation indicator (red LED)
Ambient temperature		Operating: –25°C to 70°C (with no icing)
Ambient humidity		Operating: 35% to 95%
Temperature influence		±10% max. of sensing distance at 23°C in temperature range of –25°C to 70°C
Voltage influence		±2.5% max. of sensing distance in rated voltage range ±15%
Residual voltage		3.3 V max. (with 100 mA load current and 2-m cable)
Insulation resistance		50 MΩ min. (at 500 VDC) between current carry parts and case
Dielectric strength		1,000 VAC for 1 min between current carry parts and case
Vibration resistance		Destruction: 10 to 55 Hz, 1.5-mm double amplitude for 2 hrs each in X, Y, and Z directions
Shock resistance		Destruction: 500 m/s ² (approx. 50G) for 3 times each in X, Y, and Z directions
Enclosure ratings		IEC IP67 (JEM IP67G (water-tight, oil-tight)
Weight (with 2-m cable)		Approx. 45 g
Material	Case	Heat-resistive ABS resin
	Sensing surface	

Note: The response frequency in the table is a mean value obtained under the following conditions.
 Location of each standard sensing object: At a distance half as long as the sensing distance of the sensor.
 Distance between any two adjacent standard sensing objects: Twice as wide as the width of the standard sensing object.


DC 3-wire

Item		TL-W1R5M	TL-W3M	TL-W5M	TL-W5	TL-W20M
Sensing distance		1.5 mm ±10%	3 mm ±10%	5 mm ±10%		20 mm ±10%
Supply voltage (operating voltage range)		12 to 24 VDC (10 to 30 VDC), ripple (p-p): 10% max.			12 to 24 VDC (10 to 30 VDC), ripple (p-p): 20% max.	12 to 24 VDC (10 to 30 VDC)
Current consumption (leakage current)		15 mA max. at 24 VDC (no-load)		10 mA max.	15 mA max. at 24 VDC (no-load)	8 mA at 12 VDC, 15 mA at 24 VDC
Sensing object		Magnetic metals (Non-magnetic metals can be detected if they are located close to the sensor. Refer to "Engineering Data" for details)				
Setting distance (standard sensing object)		0 to 1.2 mm (iron, 8 x 8 x 1 mm)	0 to 2.4 mm (iron, 12 x 12 x 1 mm)	0 to 4 mm (iron, 18 x 18 x 1 mm)		0 to 16 mm (iron, 50 x 50 x 1 mm)
Differential travel		10% max. of sensing distance				1% to 15% of sensing distance
Response frequency (see note)		1 kHz	600 Hz min.	500 Hz min.	300 Hz min.	40 Hz
Operating mode (for detecting sensing objects)		Load ON			E1 models: Output signal low, load ON E2 models: Output signal high, load OFF F1 models: Output signal high, load ON F2 models: Output signal low, load OFF	
Control output (switching capacity)		NPN or PNP open collector, 100 mA max.		NPN or PNP open collector, 50 mA max. at 12 VDC, 100 mA max. at 24 VDC	200 mA max.	100 mA max. at 12 VDC, 200 mA max. at 24 VDC
Circuit protection		Reverse connection protection				---
Ambient temperature		Operating: -25°C to 70°C (with no icing)				
Ambient humidity		Operating: 35% to 95%				
Temperature influence		±10% max. of sensing distance at 23°C in temperature range of -25°C to 70°C				
Voltage influence		±2.5% max. of sensing distance in rated voltage range ±10%		±2.5% max. of sensing distance in rated voltage range ±20%	±2.5% max. of sensing distance in rated voltage range ±10%	
Residual voltage		1.0 V max. (with 100 mA load current and 2-m cable)		1.0 V max. (with 50 mA load current and 2-m cable)	2.0 V max. (with 200 mA load current and 2-m cable)	1.0 V max. (with 200 mA load current and 2-m cable)
Insulation resistance		50 MΩ min. (at 500 VDC) between current carry parts and case				
Dielectric strength		1,000 VAC, 50/60 Hz for 1 min between current carry parts and case				
Vibration resistance		Destruction: 10 to 55 Hz, 1.5-mm double amplitude for 2 hrs each in X, Y, and Z directions				
Shock resistance		Destruction: 500 m/s ² (approx. 50G) for 3 times each in X, Y, and Z directions				Destruction: 500 m/s ² (approx. 50G) for 10 times each in X, Y, and Z directions
Enclosure ratings		IEC IP67 (JEM IP67G (water-tight, oil-tight))				
Weight (with 2-m cable)		Approx. 30 g		Approx. 45 g	Approx. 70 g	Approx. 180 g
Material	Case	ABS resin			ADC (Al die-cast)	Heat-resistive ABS
	Sensing surface	ABS resin				


Engineering Data

Operating Range (Typical)


TL-W1R5M




TL-W3M




TL-W5M



TL-W5




TL-W20M




Sensing Distance vs. Size and Material of Sensing Object (Typical)


TL-W1R5M




TL-W3M




TL-W5M



TL-W5



TL-W20M





Operation

■ Output Circuits

DC 2-wire

TL-W5MD□




Note: The load can be connected as shown in the above diagram.

DC 3-wire

TL-W1R5MC1


TL-W3MC□

TL-W5MC□




TL-W5E□

TL-W20ME□



TL-W5F□




Note: Maximum load current: 100 mA

Note: 1. Maximum load current: 200 mA
2. Current flows in this direction if the circuit incorporates the transistor.

TL-W1R5MB1

TL-W3MB□


TL-W5MB1




■ Timing Chart

DC 2-wire

NO Model




NC Model




DC 3-wire


TL-W1R5M□1
TL-W3M□
TL-W5M□



TL-W5□
TL-W20ME□







TL-W5F□



Dimensions


Note: All units are in millimeters unless otherwise indicated.

TL-W1R5M□1






Note: Round vinyl-insulated cable (2.9 dia., 0.12 dia. x 12, 3 cores)
Standard length: 2 m (oil-tight)

Mounting Bracket (Attachment)




Note: Mounting dimensions:
17±0.2

TL-W3M□□



Note: Round vinyl-insulated cable (2.9 dia., 0.12 dia. x 12, 3 cores)
Standard length: 2 m (oil-tight)




Mounting Bracket (Attachment)



Note: Mounting dimensions:
17±0.2

TL-W5M□□

TL-W5MD□□





TL-W5M□□:
Round vinyl-insulated cable (4 dia., 0.12 dia. x 18, 3 cores)
Standard length: 2 m (oil-tight)

TL-W5MD□□:
Round vinyl-insulated cable (4 dia., 0.12 dia. x 27, 2 cores)
Standard length: 2 m (oil-tight)


Two, 3.5 x 5 mounting holes

TL-W5E□



TL-W5F□



Mounting Holes



TL-W20ME□




Precautions

Effects of Surrounding Metals


Provide a minimum distance as shown in the table below between the TL-W and the surrounding metals to prevent the TL-W from being induced by the metals and malfunctioning or being affected by the heat radiated by the metals.

Model	ℓ	m	n
TL-W1R5M□1	2 mm	0 mm	8 mm
TL-W3M	3 mm	0 mm	12 mm
TL-W5MD	5 mm	0 mm	20 mm
TL-W5MC/MB	5 mm	0 mm	20 mm
TL-W20ME	25 mm	16 mm	100 mm
TL-W5E/F	0 mm	0 mm	20 mm

Metal on a Single Side
(not exceeding the height of the sensor head)



Metals on Both Sides and in front of the Sensor




Mutual Interference

Be sure to space the two sensors at a distance greater than that shown in the table to prevent mutual interference.

Model	A	B
TL-W1R5M□1	75 (50) mm	25 (8) mm
TL-W3M	90 (60) mm	30 (10) mm
TL-W5MD	120 (80) mm	60 (30) mm
TL-W5MC/MB	120 (80) mm	60 (30) mm
TL-W20ME	200 (100) mm	200 (100) mm
TL-W5E/F	50 mm	35 mm

Note: The above values in parentheses are applicable when using two sensors with different frequencies.



Mounting

Use M3 flat-head screws to mount the TL-W1R5M□1 and TL-W3M□1.

The resin cover should be tightened to 10 kgf • cm (0.98 N • m) maximum.

ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.

To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

Cat. No. E221-E1-2 In the interest of product improvement, specifications are subject to change without notice.

OMRON Corporation

Systems Components Division H.Q.
28th Fl., Crystal Tower Bldg.
1-2-27, Shiromi, Chuo-ku,
Osaka 540 Japan
Phone: 06-949-6012 Fax: 06-949-6021

Printed in Japan
0196-1.5M (1291) a

