

# MGF0906B

## L, S BAND POWER GaAs FET

### DESCRIPTION

The MGF0906B, GaAs FET with an N-channel schottky gate, is designed for use in UHF band amplifiers.

### FEATURES

- Class A operation
- High output power  
 $P_{1dB} = 37\text{dBm}$  (TYP) @2.3GHz
- High power gain  
 $G_{LP} = 11\text{dB}$  (TYP) @2.3GHz
- High power added efficiency  
 $\eta_{add} = 40\%$  (TYP) @2.3GHz,  $P_{1dB}$
- Hermetically sealed metal-ceramic package with ceramic lid

### APPLICATION

UHF band power amplifiers

### QUALITY GRADE


- IG

### RECOMMENDED BIAS CONDITIONS

- $V_{DS} = 10\text{V}$
- $I_D = 1.2\text{A}$
- $R_g = 100\Omega$
- Refer to Bias Procedure

### OUTLINE DRAWING

Unit: millimeters



GF-21

- ① GATE
- ② SOURCE (FLANGE)
- ③ DRAIN

### ABSOLUTE MAXIMUM RATINGS ( $T_a = 25^\circ\text{C}$ )

| Symbol    | Parameter                  | Ratings    | Unit             |
|-----------|----------------------------|------------|------------------|
| $V_{GDO}$ | Gate to drain voltage      | -15        | V                |
| $V_{GSO}$ | Gate to source voltage     | -15        | V                |
| $I_D$     | Drain current              | 3          | A                |
| $I_{GR}$  | Reverse gate current       | -10        | mA               |
| $I_{GF}$  | Forward gate current       | +21        | mA               |
| $P_T$     | Total power dissipation *1 | 23         | W                |
| $T_{ch}$  | Channel temperature        | 175        | $^\circ\text{C}$ |
| $T_{stg}$ | Storage temperature        | -65 ~ +175 | $^\circ\text{C}$ |

\*1:  $T_c = 25^\circ\text{C}$

### ELECTRICAL CHARACTERISTICS ( $T_a = 25^\circ\text{C}$ )





| Symbol         | Parameter                            | Test conditions                                             | Limits |      |     | Unit               |
|----------------|--------------------------------------|-------------------------------------------------------------|--------|------|-----|--------------------|
|                |                                      |                                                             | Min    | Typ  | Max |                    |
| $I_{DSS}$      | Saturated drain current              | $V_{DS} = 3\text{V}, V_{GS} = 0\text{V}$                    | —      | 2.0  | 3.0 | A                  |
| $g_m$          | Transconductance                     | $V_{DS} = 3\text{V}, I_D = 1.1\text{A}$                     | —      | 1.0  | —   | S                  |
| $V_{GS(off)}$  | Gate to source cut-off voltage       | $V_{DS} = 3\text{V}, I_D = 10\text{mA}$                     | -1     | -2.5 | -4  | V                  |
| $P_{1dB}$      | Output power at 1dB gain compression | $V_{DS} = 10\text{V}, I_D = 1.2\text{A}, f = 2.3\text{GHz}$ | 35.5   | 37   | —   | dBm                |
| $G_{LP}$       | Linear power gain                    |                                                             | 10     | 11   | —   | dB                 |
| $I_D$          | Drain current                        |                                                             | —      | 1.1  | 1.5 | A                  |
| $\eta_{add}$   | Power added efficiency at $P_{1dB}$  |                                                             | —      | 40   | —   | %                  |
| $R_{th(ch-c)}$ | Thermal resistance *1                | $\Delta V_f$ method                                         | —      | —    | 6.5 | $^\circ\text{C/W}$ |

\*1: Channel to case

NOV. '97


**L, S BAND POWER GaAs FET**

**TYPICAL CHARACTERISTICS**




**L, S BAND POWER GaAs FET**

**S<sub>11</sub>, S<sub>22</sub> vs. f**



**S<sub>21</sub>, S<sub>12</sub> vs. f**



**S PARAMETERS** (Ta=25°C, V<sub>DS</sub>=10V, I<sub>D</sub>=1.2A)

| f<br>(GHz) | S <sub>11</sub> |             | S <sub>21</sub> |             | S <sub>12</sub> |             | S <sub>22</sub> |             | K     | MSG/MAG<br>(dB) |
|------------|-----------------|-------------|-----------------|-------------|-----------------|-------------|-----------------|-------------|-------|-----------------|
|            | Magn.           | Ang. (deg.) | Magn.           | Ang. (deg.) | Magn.           | Ang. (deg.) | Magn.           | Ang. (deg.) |       |                 |
| 0.5        | 0.922           | -139.9      | 4.997           | 104.1       | 0.016           | 51.5        | 0.673           | 174.9       | 0.869 | 25.0            |
| 0.6        | 0.913           | -146.2      | 4.570           | 97.5        | 0.019           | 44.9        | 0.674           | 172.5       | 0.837 | 23.8            |
| 0.7        | 0.906           | -151.8      | 4.176           | 91.5        | 0.022           | 39.3        | 0.676           | 170.4       | 0.807 | 22.8            |
| 0.8        | 0.900           | -156.8      | 3.815           | 85.9        | 0.023           | 34.6        | 0.677           | 168.6       | 0.826 | 22.1            |
| 0.9        | 0.896           | -161.2      | 3.484           | 80.9        | 0.025           | 30.7        | 0.679           | 167.0       | 0.819 | 21.4            |
| 1.0        | 0.894           | -165.0      | 3.182           | 76.3        | 0.026           | 27.7        | 0.680           | 165.7       | 0.834 | 20.9            |
| 1.1        | 0.892           | -168.4      | 2.909           | 72.2        | 0.026           | 25.2        | 0.680           | 164.5       | 0.883 | 20.5            |
| 1.2        | 0.891           | -171.4      | 2.662           | 68.3        | 0.027           | 23.4        | 0.681           | 163.5       | 0.906 | 19.9            |
| 1.3        | 0.891           | -174.0      | 2.440           | 64.8        | 0.027           | 22.1        | 0.681           | 162.6       | 0.959 | 19.6            |
| 1.4        | 0.891           | -176.3      | 2.242           | 61.6        | 0.027           | 21.3        | 0.680           | 161.8       | 1.024 | 18.2            |
| 1.5        | 0.892           | -178.3      | 2.067           | 58.7        | 0.027           | 20.9        | 0.679           | 161.1       | 1.086 | 17.1            |
| 1.6        | 0.892           | -179.9      | 1.913           | 55.9        | 0.027           | 20.7        | 0.678           | 160.5       | 1.160 | 16.1            |
| 1.7        | 0.892           | -178.2      | 1.779           | 53.2        | 0.028           | 20.8        | 0.676           | 159.8       | 1.202 | 15.3            |
| 1.8        | 0.892           | -176.6      | 1.664           | 50.7        | 0.028           | 21.0        | 0.673           | 159.2       | 1.285 | 14.5            |
| 1.9        | 0.891           | -175.1      | 1.565           | 48.2        | 0.029           | 21.3        | 0.670           | 158.6       | 1.334 | 13.9            |
| 2.0        | 0.890           | -173.6      | 1.482           | 45.8        | 0.030           | 21.6        | 0.666           | 157.9       | 1.384 | 13.2            |
| 2.1        | 0.887           | -172.0      | 1.414           | 43.4        | 0.031           | 21.9        | 0.661           | 157.1       | 1.455 | 12.6            |
| 2.2        | 0.883           | -170.2      | 1.359           | 40.8        | 0.033           | 21.9        | 0.655           | 156.3       | 1.487 | 12.0            |
| 2.3        | 0.877           | -168.3      | 1.315           | 38.2        | 0.035           | 21.8        | 0.649           | 155.3       | 1.538 | 11.4            |
| 2.4        | 0.870           | -166.2      | 1.282           | 35.4        | 0.038           | 21.3        | 0.642           | 154.1       | 1.553 | 10.9            |
| 2.5        | 0.861           | -163.8      | 1.258           | 32.5        | 0.042           | 20.5        | 0.633           | 152.8       | 1.554 | 10.4            |
| 2.6        | 0.850           | -161.1      | 1.241           | 29.3        | 0.046           | 19.2        | 0.624           | 151.3       | 1.569 | 9.9             |
| 2.7        | 0.837           | -157.9      | 1.231           | 25.8        | 0.051           | 17.4        | 0.614           | 149.5       | 1.569 | 9.4             |
| 2.8        | 0.821           | -154.4      | 1.226           | 22.0        | 0.057           | 15.0        | 0.602           | 147.5       | 1.566 | 8.9             |
| 2.9        | 0.803           | -150.3      | 1.224           | 17.9        | 0.064           | 11.9        | 0.589           | 145.1       | 1.566 | 8.4             |
| 3.0        | 0.781           | -145.6      | 1.224           | 13.4        | 0.072           | 8.0         | 0.576           | 142.5       | 1.549 | 7.9             |