

THIS DRAWING IS UNPUBLISHED.




RELEASED FOR PUBLICATION

© COPYRIGHT — TE Connectivity

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	F	REVISED PER ECR-17-016350	07NOV2017	R.Z	S.L



NOTES:

1. MATERIAL:

- 1.1 HOUSING: THERMOPLASTIC, UL94 V-0, COLOR: NATURAL.
- 1.2 CONTACT: BRASS, THICKNESS=0.45mm
- 1.3 MOUNT EAR: BRASS, THICKNESS=0.3mm
- 1.4 MYLAR: POLYETHYLENE, YELLOW COLOR.


POWER	5.00mm	1, 13, 38, 50
GENERAL	4.25mm	ALL OTHER PINS
DETECT	3.50mm	25, 26
PIN TYPE	INTERFACE DIM. L	PIN NO.

AVAILABLE	REEL	WITH	GOLD FLASH	0.381um [15u"]	3-1734451-1
AVAILABLE				0.381um [15u"]	2-1734451-1
OBSOLETE	TRAY	W/O	GOLD FLASH	1-1734451-3	
OBSOLETE			MATTE-TIN 2.54um [100u"] MIN	0.762um [30u"]	1-1734451-2
AVAILABLE				0.381um [15u"]	1-1734451-1
OBSOLETE				0.762um [30u"]	1-1734451-2
AVAILABLE				0.381um [15u"]	1734451-1
STATUS	PACKAGE	MYLAR	PLATING ON SOLDER TAILS	MIN. GOLD THICKNESS	PART No.

2. FINISH:

- 2.1 CONTACT: GOLD PLATED (SEE TABLE) ON CONTACT AREA, GOLD OR MATTE-TIN PLATING (SEE TABLE) ON SOLDER TAILS, 1.27um[50u"] MIN. NICKEL UNDERPLATED OVERALL
- 2.2 MOUNT EAR: 2.54um [100u"] MIN. MATTE-TIN PLATED OVERALL 1.27um [50u"] MIN. NICKEL UNDERPLATED OVERALL.
3. CONNECTOR REQUIRES USE OF 2 - SIZE M2 SCREWS FOR FASTENING TO PRINTED CIRCUIT BOARD.
4. REFLOW SOLDER CAPABLE TO 260° PER TE CONNECTIVITY SPEC 109-201, CPMDOTOPM B.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.CHIEEN	21JAN2017	 TE Connectivity	
		CHK S.HOU	21JAN2017		
		APVD W.KODAWA	21JAN2017	NAME	
		PRODUCT SPEC			
		108-57134		COMPACT FLASH CARD CONNECTOR HEADER ASSEMBLY, 50 POS TOP MOUNT, SMT TYPE, H=4.0mm	
		APPLICATION SPEC			
		—		SIZE	CAGE CODE
		WEIGHT 2.52 GRAMS		A300779	C=1734451
		CUSTOMER DRAWING		SCALE 1:1	SHEET 1 OF 3
				REV F	



THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-




© COPYRIGHT — TE Connectivity

ALL RIGHTS RESERVED.



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

TAPE AND REEL PACKING : AS SHOWN




DETIAL A

DETAIL A
SCALE 5:1

NOTES:

- MATERIAL:
REEL: PS.
BAG: PE
BOX: CORRUGATED FIBERBOARD
- DIMENSION:
REEL: $\phi 330 \times 72$
BAG: L=850mm, W=600mm, THICKNESS=0.1mm
BOX: L=350mm, W=350mm, H=400mm
- EACH BAG SHALL BE INCLUDED:
* DESICCANT
- QUANTITY: SEE TABLE
- WEIGHT: SEE TABLE



3.76 Kg	1.26 Kg	100	5	500	3-1734451-1
8.36 Kg	2.51 Kg	200	5	1000	2-1734451-1
GROSS WEIGHT	NET WEIGHT	PCS/ REEL	REEL/ BOX	PCS/ BOX	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN S.CH IEN 21JAN2017

CHK S.HOU 21JAN2017

APVD W.KODAWA 21JAN2017

PRODUCT SPEC

108-57134

APPLICATION SPEC

—

WEIGHT 2.52 GRAMS

CUSTOMER DRAWING

STE TE Connectivity

NAME

COMPACT FLASH CARD CONNECTOR
HEADER ASSEMBLY, 50 POS
TOP MOUNT, SMT TYPE, H=4.0mm

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 00779 C-1734451

SCALE 1:1 SHEET 3 OF 3 REV F