






FCI CONFIDENTIAL




FCIconnect.com

This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI. Copyright FCI

PRODUCT NO.
61126-****/****LF



SMT IN LIN




RIGHT ANGLE

<SEC. Z-Z>



ABOVE P.C.B
LEFT PUSH ROD




ABOVE P.C.B
RIGHT PUSH ROD



BELOW P.C.B
RIGHT PUSH ROD



BELOW P.C.B
LEFT PUSH ROD



DETAIL E

FOR 61126-****H/****HLF ONLY

mat'l. code				surface	tolerance	projection	product family			
				ISO 1302	ISO 406 ISO 101					
ltr	ecn no	dr	date	tolerances unless otherwise specified			title			
F	V11056	W L	03/20/01	angles	linear	±0.30	NARROW BODY			
F	V12191	W L	09/20/01				EJ HEADER ASS'Y 68POS.			
G	T10287	W L	10/19/01	±2'						
H	N05-0063	WB	03/04/05	dr	WENDY CHEN	07/12/95	dwg no			
J	N08-0029	MZ	02/26/08	enr	L.W. LU	07/12/95	sheet 1 of 4 size			
				chr	JOSEPH HSIA	07/12/95	61126			
				appd	JENN TSAO	07/12/95	A4			
sheet		revision	J	J	J	J	type			
index		sheet	1	2	3	4	CUSTOMER Drawing			

61126-****

1

FCI CONFIDENTIAL



This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI. Copyright FCI

PRODUCT NO.
61126-****LF

LEFT	BELOW	SMT-IL	NONE	61126-602XYLF	94898-502LF	95079-00XY	NONE	LAYOUT 2
RIGHT	BELOW	SMT-IL	NONE	61126-502XYLF	94898-502LF	95079-10XY		
LEFT	ABOVE	SMT-IL	NONE	61126-102XYLF	94898-002LF	95079-10XY	NONE	LAYOUT 1
RIGHT	ABOVE	SMT-IL	NONE	61126-002XYLF	94898-002LF	95079-00XY		
RIGHT	ABOVE	SMT-IL	NONE	61126-002XYHLF④	94898-002LF	95079-00XY	93925-001	LAYOUT 4
LEFT	BELOW	R/A	5	61126-650XYLF	94898-520LF	95079-05XY	NONE	
RIGHT	BELOW	R/A	5	61126-550XYLF	94898-520LF	95079-15XY		
LEFT	ABOVE	R/A	5	61126-150XYLF	94898-020LF	95079-15XY		LAYOUT 3
LEFT	ABOVE	R/A	5	61126-150XYHLF④	94898-020LF	95079-15XY	93925-004	
RIGHT	ABOVE	R/A	7.7	61126-070XYLF ⚠	94898-077MLF	95079-07XY	NONE	
RIGHT	ABOVE	R/A	5	61126-050XYHLF ④	⚠ 94898-020MLF	95079-05XY	93925-004	
RIGHT	ABOVE	R/A	5	61126-050XYLF	94898-020LF	95079-05XY		LAYOUT 4
LEFT	BELOW	R/A	4	61126-640XYLF	94898-510LF	95079-04XY	NONE	
RIGHT	BELOW	R/A	4	61126-540XYLF	94898-510LF	95079-14XY		
LEFT	ABOVE	R/A	4	61126-140XYLF	94898-010LF	95079-14XY	NONE	LAYOUT 3
RIGHT	ABOVE	R/A	4	61126-040XYLF	94898-010LF	95079-04XY		
LEFT	BELOW	R/A	2	61126-620XYLF	94898-540LF	95079-02XY	NONE	LAYOUT 4
RIGHT	BELOW	R/A	2	61126-520XYLF	94898-540LF	95079-12XY		
LEFT	ABOVE	R/A	2	61126-120XYLF	94898-040LF	95079-12XY	NONE	LAYOUT 3
RIGHT	ABOVE	R/A	2	61126-020XYLF	94898-040LF	95079-02XY		
LEFT	BELOW	R/A	NONE	61126-600XYLF	94898-500LF	95079-00XY	NONE	LAYOUT 4
RIGHT	BELOW	R/A	NONE	61126-500XYLF	94898-500LF	95079-10XY		
LEFT	ABOVE	R/A	NONE	61126-100XYLF	94898-000LF	95079-10XY	NONE	LAYOUT 3
LEFT	ABOVE	R/A	NONE	61126-100XYHLF④	94898-000LF	95079-10XY	93925-001	
RIGHT	ABOVE	R/A	NONE	61126-000XYHLF④	94898-000LF	95079-00XY	93925-001	
RIGHT	ABOVE	R/A	NONE	61126-000XYLF	94898-000LF	95079-00XY	NONE	
① PUSH ROD LOCATION	② PCB SIDE	SOLDER TAIL	DIM. L STAND-OFF	TO MAKE FINAL ASS'Y PART NUMBER	HEADER PART NUMBER	MECHANISM ASS'Y P/N	HOLD-DOWN (4 PCS)	PCB LAYOUT SEE PAGE 3


NOTE: (CONTIONOUS FROM SHEET 2)

6. IF LEAD FREE P/N. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
SOLDER TAIL : SMT-IL, SMT-STG CAN RESIST 40 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
SOLDER TAIL : R/A CAN RESIST 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.00MM MINIMUM THICK CIRCUIT BOARD.
7. IF LEAD FREE P/N.THE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DISCRIBLED IN GS-22-008
8. LEAD FREE P/N PACKAGING MEETS GS-14-920 SPECIFICATION

mat'l. code				surface	tolerance	projection	product family
				ISO 1302	ISO 406 ISO 1101		
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
J				angles	linear ±0.30	scale 1:1	NARROW BODY EJ HEADER ASS'Y 68POS.
				±2'			
				dr	WENDY CHEN 07/12/95		dwg no
				enr	L.W. LU 07/12/95		sheet 3 of 4
				chr	JOSEPH HSIA 07/12/95		size
				appd	JENN TSAO 07/12/95		A4
sheet index		revision sheet				type CUSTOMER Drawing	


PRODUCT NO.
61126-****/****LF

TOP MOUNT HEADER ASS'Y P.C.B. LAYOUT
LAYOUT 1




4 CARD INSERTION DIRECTION
RECOMMENDED FOOT PRINT(MOUNTED SIDE)

TOP MOUNT HEADER ASS'Y P.C.B. LAYOUT
LAYOUT 3




4 CARD INSERTION DIRECTION
RECOMMENDED FOOT PRINT(MOUNTED SIDE)

BOTTOM MOUNT HEADER ASS'Y P.C.B. LAYOUT
LAYOUT 2



4 CARD INSERTION DIRECTION
RECOMMENDED FOOT PRINT(MOUNTED SIDE)

BOTTOM MOUNT HEADER ASS'Y P.C.B. LAYOUT
LAYOUT 4



4 CARD INSERTION DIRECTION
RECOMMENDED FOOT PRINT(MOUNTED SIDE)

mat'l. code				surface	tolerance	projection	product family
ltr				ISO 1302	ISO 406 ISO 101		NARROW BODY EJ HEADER ASS'Y 68POS.
ecn no				tolerances unless otherwise specified		MM	
dr				angles	linear	scale 1:1	
date				±2'	±0.30		
J							dwg no 61126 sheet 4 of 4 size A4
				dr	WENDY CHEN	07/12/95	
				enr	L.W. LU	07/12/95	
				chr	JOSEPH HSIA	07/12/95	
				appd	JENN TSAO	07/12/95	type CUSTOMER Drawing
sheet index				revision sheet			