





LOC	DIST	REVISIONS				
		PR	LTR	DESCRIPTION	DATE	DWN APVD
GP	00	J1		REVISED PER ECO-11-004835	11MAR11	RK HMR

1. WIRE RANGE 0.13–0.35 mm² (26–22 AWG).
2. INSULATION RANGE: 0.89–1.65 [.035–.065] DIA LARGER SIZES OF 0.68–1.91 [.066–.075] DIA INSULATION REQUIRE WIRE AND CRIMP EVALUATION FROM AMP INCORPATED.
3. DIMENSIONS IN BRACKETS ARE IN INCHES.
- 4

0.00076 [.000030] MIN THK GOLD STRIPES IN LOCALIZED PLATE AREA ON BEAM AND DIMPLE OVER 0.00127 [.000050] MIN THK NICKEL OVER ENTIRE CONTACT
–OR–
OR GOLD FLASH OVER PALLADIUM–NICKEL STRIPES, .00076 [.000030] MIN THK TOTAL IN LOCALIZED PLATE AREA ON BEAM AND DIMPLE OVER .00127 [.000050] MIN NICKEL OVER ENTIRE CONTACT.
- 5

AFTER PACKAGING AND SHIPMENT, A LANCE HEIGHT 0.46–0.71 [.018–.030] IS PERMISSABLE.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. BECK 01MAR91	770666-2	
		CHK R. SWING 01MAR91	PRE-TIN	
DIMENSIONS: mm [INCHES]		APVD D. CLARK 05MAR91	FINISH	
		PRODUCT SPEC	PART NO.	
MATERIAL 0.198 [.0078] PH BRZ		APPLICATION SPEC	RECEPTACLE, CST-100, LOOSE PIECE	
		WEIGHT		
CUSTOMER DRAWING		SCALE 10:1	SHEET 1 OF 1	REV J1