



FEATURES:

- Banana Plug provides vertical and cross stacking.
- Provides a Banana Plug output from a barrier strip or binding post.
- Ideal for connection to power supplies and test equipment.
- Both ends will mate to Model #3750 or any standard binding post.

MATERIALS:

Spade Lug & Banana Plug

Material: Brass per QQ-B-626, Alloy 360, 1/2 Hard, Banana Plug spring – Nickel plated Beryllium Copper
Finish: Nickel plated per QQ-N-290, Class 2, 200/300 microinches.

Insulation: Polypropylene molded to spade lug body and wire. Color matches color of wire.

Wire: 18 AWG stranding 65 x 36 t.c., PVC insulated 3.66 (.144) O.D.

Color: See Ordering Information.

Marking: "POMONA 1370-*."

RATINGS:

Operating Temperature: +55°C. (+131°F.) Max.

Operating Voltage: 5000 VDC Max.

Current: 15 Amperes

ORDERING INFORMATION: Model 1370-XX-*

XX = Cable Lengths, Standard Lengths: 12" (305), 24" (610), 36" (914), 48" (1219) & 60" (1524). Additional lengths and colors can be quoted upon request.

*= Color, -0 Black, -2 Red. Ordering Example: 1370-60-2 Indicates 60" in length, color is Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[1370-48-0](#) [1370-48-2](#) [1370-12-2](#) [1370-12-0](#) [1370-197-0](#) [1370-60-0](#) [1370-60-2](#) [1370-24-0](#) [1370-24-2](#) [1370-36-2](#)
[1370-36-0](#)