

5A, 20V - 200V Surface Mount Schottky Barrier Rectifiers

FEATURES

- Low power loss, high efficiency
- Ideal for automated placement
- Guardring for overvoltage protection
- High surge current capability
- Compliant to RoHS Directive 2011/65/EU and in accordance to WEEE 2002/96/EC
- Halogen-free according to IEC 61249-2-21 definition



MECHANICAL DATA

Case: DO-214AB (SMC)

Molding compound, UL flammability classification rating 94V-0

Moisture sensitivity level: level 1, per J-STD-020

Part No. with suffix "H" means AEC-Q101 qualified

Packing code with suffix "G" means green compound (halogen-free)

Terminal: Matte tin plated leads, solderable per JESD22-B102

Meet JESD 201 class 2 whisker test

Polarity: Indicated by cathode band

Weight: 0.21 g (approximately)

DO-214AB (SMC)

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS (T _A =25°C unless otherwise noted)											
PARAMETER	SYMBOL	SK 52C	SK 53C	SK 54C	SK 55C	SK 56C	SK 59C	SK 510C	SK 515C	SK 520C	Unit
Maximum repetitive peak reverse voltage	V _{RRM}	20	30	40	50	60	90	100	150	200	V
Maximum RMS voltage	V _{RMS}	14	21	28	35	42	63	70	105	140	V
Maximum DC blocking voltage	V _{DC}	20	30	40	50	60	90	100	150	200	V
Maximum average forward rectified current	I _{F(AV)}	5									A
Peak forward surge current, 8.3 ms single half sine-wave superimposed on rated load	I _{FSM}	120									A
Maximum instantaneous forward voltage (Note 1) I _F = 5 A	V _F	0.55			0.75		0.85		0.95		V
Maximum reverse current @ rated V _R T _J =25°C T _J =100°C T _J =125°C	I _R	0.5					0.3				mA
		20			10		-				
		-			-		5				
Voltage rate of change (Rated V _R)	dV/dt	10000									V/μs
Typical thermal resistance	R _{θJL}	17									°C/W
	R _{θJA}	50									
Operating junction temperature range	T _J	- 55 to +150									°C
Storage temperature range	T _{STG}	- 55 to +150									°C

Note 1: Pulse test with PW=300μs, 1% duty cycle

ORDERING INFORMATION					
PART NO.	PART NO. SUFFIX	PACKING CODE	PACKING CODE SUFFIX	PACKAGE	PACKING
SK5xxC (Note 1)	H	R7	G	SMC	850 / 7" Plastic reel
		R6		SMC	3,000 / 13" Paper reel
		M6		SMC	3,000 / 13" Plastic reel

Note 1: "xx" defines voltage from 20V (SK52C) to 200V (SK520C)

EXAMPLE					
PREFERRED PART NO.	PART NO.	PART NO. SUFFIX	PACKING CODE	PACKING CODE SUFFIX	DESCRIPTION
SK56CHR7G	SK56C	H	R7	G	AEC-Q101 qualified Green compound

RATINGS AND CHARACTERISTICS CURVES

(T_A=25°C unless otherwise noted)

FIG.1 FORWARD CURRENT DERATING CURVE




FIG. 2 MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT




FIG. 3 TYPICAL FORWARD CHARACTERISTICS




FIG. 4 TYPICAL REVERSE CHARACTERISTICS




FIG. 5 TYPICAL JUNCTION CAPACITANCE






FIG. 6 TYPICAL TRANSIENT THERMAL IMPEDANCE




PACKAGE OUTLINE DIMENSIONS
DO-214AB (SMC)



DIM.	Unit (mm)		Unit (inch)	
	Min	Max	Min	Max
A	2.90	3.20	0.114	0.126
B	6.60	7.11	0.260	0.280
C	5.59	6.22	0.220	0.245
D	2.00	2.62	0.079	0.103
E	1.00	1.60	0.039	0.063
F	7.75	8.13	0.305	0.320
G	0.10	0.20	0.004	0.008
H	0.15	0.31	0.006	0.012

SUGGESTED PAD LAYOUT



Symbol	Unit (mm)	Unit (inch)
A	3.3	0.130
B	2.5	0.098
C	6.8	0.268
D	4.4	0.173
E	9.4	0.370

MARKING DIAGRAM



- P/N = Specific Device Code
- G = Green Compound
- YW = Date Code
- F = Factory Code

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Taiwan Semiconductor:

[SK510C](#) [SK515C](#) [SK52C](#) [SK55C](#) [SK59C](#) [SK53C](#) [SK54C](#) [SK56C](#) [SK520C R6](#) [SK520C R7](#) [SK59C R7](#) [SK510C R6](#) [SK53C R7](#) [SK52CHR6](#) [SK52CHR6G](#) [SK52C R7](#) [SK52C R7G](#) [SK515CHR6](#) [SK59CHR6G](#) [SK59CHR7G](#) [SK54CHR6G](#) [SK510CHR7G](#) [SK510CHR6G](#) [SK515C R7G](#) [SK520CHR7G](#) [SK52C R6G](#) [SK55C R6G](#) [SK515C R6](#) [SK54C R7G](#) [SK53C R7G](#) [SK520CHR7](#) [SK520C R6G](#) [SK515CHR7](#) [SK510C R6G](#) [SK510CHR6](#) [SK54C R6](#) [SK55C R7](#) [SK54CHR6](#) [SK55C R7G](#) [SK59CHR7](#) [SK515C R6G](#) [SK53C R6G](#) [SK510C R7](#) [SK59CHR6](#) [SK52C R6](#) [SK59C R7G](#) [SK515CHR7G](#) [SK59C R6G](#) [SK56C R7G](#) [SK54CHR7](#) [SK55CHR6](#) [SK56C R6G](#) [SK52CHR7](#) [SK515CHR6G](#) [SK55C R6](#) [SK52CHR7G](#) [SK53CHR6G](#) [SK56CHR6](#) [SK515C R7](#) [SK54C R6G](#) [SK520CHR6G](#) [SK520C R7G](#) [SK55CHR7](#) [SK53CHR7](#) [SK53CHR6](#) [SK510C R7G](#) [SK54CHR7G](#) [SK56CHR7](#) [SK56C R7](#) [SK520CHR6](#) [SK53CHR7G](#) [SK59C R6](#) [SK56CHR7G](#) [SK56CHR6G](#) [SK510CHR7](#) [SK55CHR6G](#) [SK55CHR7G](#)