

# CAT3606

## 6-Channel Low Noise Charge Pump White LED Driver

### Description

The CAT3606 controls up to four LEDs for the main display and two LEDs for the sub-display in cellular phones. The device is capable of operating in either 1x (LDO) mode or 1.5x charge pump mode. All LED pin currents are regulated and tightly matched to achieve uniformity of brightness across the LCD backlight. An external resistor ( $R_{SET}$ ) sets the nominal output current.

The device can deliver as much as 20 mA per channel during low voltage operation (3 V), and 30 mA per channel during nominal operation (3.3 V). A constant high-frequency switching scheme (1 MHz) provides low noise and allows the use of very small value ceramic capacitors.

A “zero” quiescent current mode can be achieved via the chip enable pin EN. The Main and Sub LEDs each have their own dedicated ON/OFF control pins ENM, ENS. Dimming can be achieved using either a DC voltage to control the  $R_{SET}$  pin current, or by applying a PWM signal on the  $\overline{ENM}$  and  $\overline{ENS}$  pins.

The device is available in a 16-pad TQFN package with a max height of 0.8 mm.

### Features

- Drives up to 4 Main LEDs and 2 Sub LEDs
- Separate Control for Main and Sub LEDs
- Compatible with Supply Voltage of 3 V to 5.5 V
- Power Efficiency up to 90%
- Output Current up to 30 mA per LED
- High-frequency Operation at 1 MHz
- 2 Modes of Operation 1x and 1.5x
- White LED Detect Circuitry on All Channels
- Shutdown Current less than 1  $\mu$ A
- Small Ceramic Capacitors
- Soft Start and Current Limiting
- Short Circuit Protection
- 16-pad TQFN Package, 0.8 mm Max Height
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

### Applications

- Cell Phone Main and Sub-display Backlight
- Navigation
- PDAs
- Digital Cameras




ON Semiconductor®

<http://onsemi.com>



TQFN-16  
HV4 SUFFIX  
CASE 510AE

### PIN CONNECTIONS (Note 1)



### MARKING DIAGRAMS




G366 = CAT3606HV4-T2  
CDBB = CAT3606HV4-GT2

### ORDERING INFORMATION

| Device         | Package             | Shipping              |
|----------------|---------------------|-----------------------|
| CAT3606HV4-T2  | TQFN-16<br>(Note 2) | 2,000/<br>Tape & Reel |
| CAT3606HV4-GT2 | TQFN-16<br>(Note 3) |                       |

1. The “exposed pad” under the package must be connected to the ground plane on the PCB.
2. Matte-Tin Plated Finish (RoHS-compliant).
3. NiPdAu Plated Finish (RoHS-compliant).

**CAT3606**

### Figure 1. Typical Application Circuit

### Table 1. PIN DESCRIPTION

| Pin # | Name                    | Function                                                                 |
|-------|-------------------------|--------------------------------------------------------------------------|
| 1     | LED6                    | LED6 cathode terminal                                                    |
| 2     | EN                      | Enable/shutdown input, active high                                       |
| 3     | $\overline{\text{ENM}}$ | Enable “main” input for LED1 to LED4, active low                         |
| 4     | $\overline{\text{ENS}}$ | Enable “sub” input for LED5 and LED6, active low                         |
| 5     | RSET                    | The LED output current is set by the current sourced out of the RSET pin |
| 6     | VOUT                    | Charge pump output connected to the LED anodes                           |
| 7     | VIN                     | Supply voltage                                                           |
| 8     | C1+                     | Bucket capacitor 1 terminal                                              |
| 9     | C1                      | Bucket capacitor 1 terminal                                              |
| 10    | C2                      | Bucket capacitor 2 terminal                                              |
| 11    | C2+                     | Bucket capacitor 2 terminal                                              |
| 12    | LED1                    | LED 1 cathode terminal                                                   |
| 13    | LED2                    | LED 2 cathode terminal                                                   |
| 14    | LED3                    | LED 3 cathode terminal                                                   |
| 15    | LED4                    | LED 4 cathode terminal                                                   |
| 16    | LED5                    | LED 5 cathode terminal                                                   |
| PAD   | GND                     | Ground reference                                                         |

**Table 2. ABSOLUTE MAXIMUM RATINGS**

| Parameter                              | Rating      | Unit |
|----------------------------------------|-------------|------|
| VIN, VOUT, LEDx voltage                | −0.3 to 7.0 | V    |
| EN, ENM, ENS voltage                   | −0.3 to VIN | V    |
| RSET voltage                           | −0.3 to VIN | V    |
| RSET current                           | ±1          | mA   |
| Ambient Temperature Range              | −40 to +85  | °C   |
| Storage Temperature Range              | −65 to +160 | °C   |
| Lead Temperature                       | 300         | °C   |
| ESD Rating HBM (Human Body Model)      | 2,000       | V    |
| ESD Rating MM (Machine Model) (Note 4) | 200         | V    |

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

4. Machine model is with 200 pF capacitor discharged directly into each pin.

**Table 3. RECOMMENDED OPERATING CONDITIONS**

| Parameter                      | Range          | Unit |
|--------------------------------|----------------|------|
| VIN                            | 3.0 to 5.5     | V    |
| Ambient Temperature Range      | −40 to +85     | °C   |
| Input/Output/Bucket Capacitors | 1 ±20% Typical | μF   |
| ILED per LED pin               | 0 to 30        | mA   |
| IOUT Total Output Current      | 0 to 150       | mA   |

**Table 4. ELECTRICAL OPERATING CHARACTERISTICS**

(Limits over recommended operating conditions unless specified otherwise. Typical values at TA = 25°C, VIN = 3.5 V, IRSET = 5 μA.)

| Symbol   | Parameter                                     | Conditions                 | Min  | Typ  | Max  | Unit |
|----------|-----------------------------------------------|----------------------------|------|------|------|------|
| IQ       | Quiescent Current                             | VEN = 0 V                  |      | 0.1  | 1    | μA   |
|          |                                               | 1x Mode, No Load           |      | 0.3  | 1    | mA   |
|          |                                               | 1.5x Mode, No Load         |      | 2.6  | 5    | mA   |
| VRSET    | RSET Regulated Voltage                        |                            | 1.17 | 1.2  | 1.23 | V    |
| ILED     | Programmed LED Current                        | IRSET = 5 μA               |      | 2.4  |      | mA   |
|          |                                               | IRSET = 37 μA              |      | 15.0 |      |      |
|          |                                               | IRSET = 78 μA              |      | 30.0 |      |      |
| ILED     | LED Current Range with 6 LEDs                 | 3.3 ≤ VIN ≤ 4.5 V          |      |      | 30   | mA   |
|          |                                               | 3.0 ≤ VIN ≤ 4.5 V          |      |      | 20   |      |
| ILED     | LED Current Range with 4 LEDs                 | 3.3 ≤ VIN ≤ 4.5 V          |      |      | 30   | mA   |
| ILED-ACC | LED Current Accuracy                          | 0.5 mA ≤ ILED ≤ 3 mA       |      | ±15  |      | %    |
|          |                                               | 3 mA ≤ ILED ≤ 30 mA        |      | ±5   |      |      |
| ILED-DEV | LED Channel Matching                          | (ILED − ILEDAVG) / ILEDAVG |      | ±3   |      | %    |
| ROUT     | Output Resistance<br>(Open Loop)              | 1x Mode,                   |      | 1.4  | 2.5  | Ω    |
|          |                                               | 1.5x Mode, IOUT = 100 mA   |      | 6.5  | 10   |      |
| fOSC     | Charge Pump Frequency                         |                            | 0.8  | 1.0  | 1.3  | MHz  |
| TDROPOUT | 1x to 1.5x Mode Transition Dropout Delay      |                            | 0.4  | 0.6  | 0.9  | ms   |
| IEN-CTR  | Input Leakage Current                         | On Inputs EN, ENM, ENS     |      |      | 1    | μA   |
| VEN-CTR  | High Detect Threshold<br>Low Detect Threshold | On Inputs EN, ENM, ENS     |      | 0.8  | 1.3  | V    |
|          |                                               |                            | 0.4  | 0.7  |      |      |
| ISC      | Input Current Limit                           | VOUT = GND                 | 30   | 45   | 60   | mA   |
| ILIM     | Maximum Input Current                         | VOUT > 1 V                 | 200  | 400  | 600  | mA   |

# CAT3606

## Block Diagram




Figure 2. CAT3606 Functional Block Diagram

## Basic Operation

At power-up, the CAT3606 starts operation in 1x mode. If it is able to drive the programmed LED current, it continues in 1x mode. If the battery voltage drops to a level where the LED current cannot be met, the driver automatically switches into 1.5x mode, to boost the output voltage high enough to achieve the nominal LED current.

The above sequence is reinitialized each and every time the chip is powered up or is taken out of shutdown mode (via EN pin). The use of the Main and Sub display enable pins ( $\overline{\text{ENM}}$  or  $\overline{\text{ENS}}$ ) does not affect the mode of operation.

## LED Current Setting

The LED current is set by the external resistor  $R_{\text{SET}}$  connected between the RSET pin and ground. Table 5 lists various LED currents and the associated  $R_{\text{SET}}$  resistor value for standard 1% precision surface mount resistors.

**Table 5. RSET Resistor Selection**

| LED Current (mA) | $R_{\text{SET}}$ (k $\Omega$ ) |
|------------------|--------------------------------|
| 1                | 649                            |
| 2                | 287                            |
| 5                | 102                            |
| 10               | 49.9                           |
| 15               | 32.4                           |
| 20               | 23.7                           |
| 30               | 15.4                           |

The enable lines  $\overline{\text{ENM}}$  and  $\overline{\text{ENS}}$  allow to turn On or Off a group of LEDs as shown in Table 6.

**Table 6. LED Selection**

| Control Lines |                         |                         | LED Outputs         |                    |
|---------------|-------------------------|-------------------------|---------------------|--------------------|
| EN            | $\overline{\text{ENM}}$ | $\overline{\text{ENS}}$ | Main<br>LED1 – LED4 | Sub<br>LED5 – LED6 |
| 0             | X                       | X                       | –                   | –                  |
| 1             | 1                       | 1                       | –                   | –                  |
| 1             | 0                       | 1                       | ON                  | –                  |
| 1             | 1                       | 0                       | –                   | ON                 |
| 1             | 0                       | 0                       | ON                  | ON                 |

NOTES: 1 = logic high (or VIN)  
 0 = logic low (or GND)  
 – = LED output OFF  
 X = don't care


The unused LED channels can also be turned off by connecting the respective LED pins to VOUT. In which case, the corresponding LED driver is disabled and the typical LED sink current is only about 0.2 mA. When the following equation is true on any channel, the driver turns off the LED channel:

$$V_{\text{OUT}} - V_{\text{LED}} \leq 1 \text{ V (LED channel OFF)}$$


**Note:** The CAT3606 is designed to drive LEDs with forward voltage greater than 1 V and is not compatible with resistive loads.

# TYPICAL CHARACTERISTICS


( $V_{IN} = 3.6\text{ V}$ ,  $EN = V_{IN}$ ,  $ENM = ENS = GND$ ,  $C_{IN} = C_{OUT} = 1\text{ }\mu\text{F}$ ,  $R_{SET} = 24\text{ k}\Omega$  (20 mA per LED),  $T_{AMB} = 25^\circ\text{C}$ , unless otherwise specified.)




**Figure 3. Efficiency vs. Input Voltage (6 LEDs)**




**Figure 4. Efficiency vs. Total LED Current (6 LEDs)**




**Figure 5. LED Current vs. Input Voltage**



**Figure 6. LED Current Change vs. Temperature**




**Figure 7. Ground Current vs. Input Voltage (1x Mode)**




**Figure 8. Ground Current vs. Temperature (1x Mode)**

# TYPICAL CHARACTERISTICS


( $V_{IN} = 3.6\text{ V}$ ,  $EN = V_{IN}$ ,  $\overline{ENM} = \overline{ENS} = \text{GND}$ ,  $C_{IN} = C_{OUT} = 1\text{ }\mu\text{F}$ ,  $R_{SET} = 24\text{ k}\Omega$  (20 mA per LED),  $T_{AMB} = 25^\circ\text{C}$ , unless otherwise specified.)




**Figure 9. Ground Current vs. Input Voltage (1.5x Mode)**




**Figure 10. Supply Current vs. Input Voltage**




**Figure 11. Oscillator Frequency vs. Input Voltage**



**Figure 12. Oscillator Frequency vs. Temperature**



**Figure 13. Output Resistance vs. Input Voltage (1x Mode)**



**Figure 14. Output Resistance vs. Input Voltage (1.5x Mode)**

TYPICAL CHARACTERISTICS

( $V_{IN} = 3.6\text{ V}$ ,  $EN = V_{IN}$ ,  $ENM = ENS = GND$ ,  $C_{IN} = C_{OUT} = 1\text{ }\mu\text{F}$ ,  $R_{SET} = 24\text{ k}\Omega$  (20 mA per LED),  $T_{AMB} = 25^\circ\text{C}$ , unless otherwise specified.)




Figure 15. Switching Waveforms in 1.5x Mode




Figure 16. Operating Waveforms in 1x Mode




Figure 17. Power Up 6 LEDs at 15 mA,  
 $V_{IN} = 3\text{ V}$  (1.5x Mode)




Figure 18. Power Up 6 LEDs at 15 mA,  
 $V_{IN} = 3.6\text{ V}$  (1x Mode)




Figure 19. LED Current vs.  $R_{SET}$




Figure 20. Line Transient Response  
in 1x Mode

# TYPICAL CHARACTERISTICS

( $V_{IN} = 3.6\text{ V}$ ,  $EN = V_{IN}$ ,  $\overline{ENM} = \overline{ENS} = \text{GND}$ ,  $C_{IN} = C_{OUT} = 1\text{ }\mu\text{F}$ ,  $T_{AMB} = 25^\circ\text{C}$ , unless otherwise specified.)




Figure 21. Foldback Current Limiting




Figure 22. RSET Pin Voltage vs. Temperature




Figure 23. PWM Dimming at 1 kHz on  $\overline{ENM}$  and  $\overline{ENS}$

## Recommended Layout

When the driver is in the 1.5x charge pump mode, the 1 MHz switching frequency operation requires to minimize trace length and impedance to ground on all 4 capacitors. A ground plane should cover the area on the bottom side of the PCB opposite to the IC and the bypass capacitors. Capacitors  $C_{in}$  and  $C_{out}$  require short connection to ground which can be done with multiple vias as shown on Figure 24. A square copper area matches the QFN16 exposed pad (GND) and must be connected to the ground plane underneath. The use of multiple via will improve the heat dissipation.





Figure 24. PCB Layout

# CAT3606

## PACKAGE DIMENSIONS


TQFN16, 4x4  
CASE 510AE-01  
ISSUE A



| SYMBOL | MIN      | NOM  | MAX  |
|--------|----------|------|------|
| A      | 0.70     | 0.75 | 0.80 |
| A1     | 0.00     | 0.02 | 0.05 |
| A3     | 0.20 REF |      |      |
| b      | 0.25     | 0.30 | 0.35 |
| D      | 3.90     | 4.00 | 4.10 |
| D2     | 2.00     | ---  | 2.25 |
| E      | 3.90     | 4.00 | 4.10 |
| E2     | 2.00     | ---  | 2.25 |
| e      | 0.65 BSC |      |      |
| L      | 0.45     | ---  | 0.65 |


### Notes:

- (1) All dimensions are in millimeters.
- (2) Complies with JEDEC MO-220.



# CAT3606

## Example of Ordering Information (Note 7)



5. All packages are RoHS-compliant (Lead-free, Halogen-free).
6. The standard lead finish is NiPdAu.
7. The device used in the above example is a CAT3606HV4-GT2 (TQFN, NiPdAu Plated Finish, Tape & Reel, 2,000/Reel).
8. For Matte-Tin package option, please contact your nearest ON Semiconductor Sales office.
9. For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

ON Semiconductor and  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## PUBLICATION ORDERING INFORMATION

### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor  
P.O. Box 5163, Denver, Colorado 80217 USA  
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada  
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada  
Email: [orderlit@onsemi.com](mailto:orderlit@onsemi.com)

**N. American Technical Support:** 800-282-9855 Toll Free  
USA/Canada  
**Europe, Middle East and Africa Technical Support:**  
Phone: 421 33 790 2910  
**Japan Customer Focus Center**  
Phone: 81-3-5773-3850

**ON Semiconductor Website:** [www.onsemi.com](http://www.onsemi.com)

**Order Literature:** <http://www.onsemi.com/orderlit>

For additional information, please contact your local Sales Representative