

MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91 929

SWITCH — BASIC

CATALOG LISTING

V3-370

CK-D3469

REPLACES X101481-V3

RELEASE NO. PR-22590

CATALOG LISTING

V3-370

PAGE 1 OF 1

M

ISSUE
2

REPLACES X101481-V3

RELEASE NO. PR-22590

PAGE 1 OF 1

M

ISSUE
2

CHECK

REVISIONS

A 0005782

RJ
04 JUN 04

REVISIONS

RJ
04 JUN 04

CHECK

REVISIONS

RJ
04 JUN 04

CHECK

REVISIONS

RJ
04 JUN 04

CHECK

REVISIONS

RJ
04 JUN 04

CHECK


REVISIONS

RJ
04 JUN 04

CHECK

REVISIONS

RJ
04 JUN 04




NOTES

- 1 — TERMINALS ARE PLATED FOR SOLDERING
- 2 — IN INSPECTION, DO NOT BURN OUT — GOLD CONTACTS
- 3 — IN INSPECTION, DO NOT EXCEED 10 VDC, .1A RESISTIVE LOAD
- 4 — INSPECT SWITCH RESISTANCE PER CONTROL PLAN

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE — — — 150 GRAMS MAX
RELEASE FORCE — — — 25 GRAMS MIN
DIFFERENTIAL TRAVEL — — — .002 — .010
OVERTRAVEL — — — — — .050 MIN
FREE POSITION — — — — — .625 MAX
RELEASE TRAVEL — — — — — .010 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

L22
1A 125 VAC

SCALE FULL

DO NOT
SCALE PRINT

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE (.0) ± .030

TWO PLACE (.00) ± .015

THREE PLACE (.000) ± .005

ANGLES ±

WEIGHT



DDM/CAD

DRAWN

DCS 15 JAN 97

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[V3-370](#)