




DESCRIPTION: 0.085 RIBBON - SOLDER CUP

	014	024	036	050
A	1.728	2.154	2.667	3.264
	43.90	54.70	67.75	82.90
B	1.004	1.429	1.929	2.538
	25.50	36.30	49.00	64.47
C	1.417	1.843	2.352	2.947
	36.00	46.80	59.74	74.85



MATERIAL:

INSULATION: PBT - UL 94V-0 RATED
CONTACTS: PHOSPHOR BRONZE
CONTACT PLATING: GOLD FLASH IN MATING AREA
BRIGHT TIN IN SOLDER AREA
SHELL: STEEL, NICKEL PLATED

ELECTRICAL:

CURRENT RATING: 1 AMPS
VOLTAGE RATING: 1,000V AC r.m.s.
INSULATION RESISTANCE: 1,000MegOhms Min. @ 500VDC
CONTACT RESISTANCE: 30MilliOhms Max.
OPERATING TEMPERATURE: -55°C TO +125°C

111-YYY-1 0 3 L 00 1

SERIES
POSITIONS
014
024
036
050
GENDER
1 = MALE
TERMINATION
0 = SOLDER CUP
SHELL PLATING
3 = NICKEL
RoHS COMPLIANT
L = LOW TEMP. PROCESS
HARDWARE
00 = NO HARDWARE
PLATING
1 = GOLD FLASH

WILL ACCEPT 26-20 AWG WIRE

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: WAYNE ROBBINS

DATE: 09-15-05

CHECKED:

DATE:

SCALE: NONE

SHEET 1 OF 2


REV 11

DWG NO. 111-YYY-103L001


RoHS COMPLIANT

NorComp


	014	024	036	050
C	1.417	1.843	2.352	2.947
	36.00	46.80	59.74	74.85




14 POSITION



36 POSITION



24 POSITION



50 POSITION

NOTEDIMENSION "C" =
CENTER TO CENTER OF MOUNTING HOLES
CENTER OF RADI
OVERALL LENGTH OF CUTOUT

RoHS COMPLIANT

DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: M. SIGMON		DATE: 01-14-11	
		CHECKED:		DATE:	
NorComp	SCALE: NONE		SHEET 2		OF 2
	DWG NO.		111-YYY-103L001		
		REV 11			