

SACC-M12MS-5CON-PG11-DUO

Order No.: 1662285

The illustration shows version SACC-M12MS-5CON-PG11-DUO-M



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1662285>

Sensor/actuator connector, male, straight, 5-pos., M12, A-coded,
screw connection, plastic knurl, cable screw connection Pg11-DUO

Commercial data

GTIN (EAN)	 4 017918 100438
sales group	D122
Pack	1 pcs.
Customs tariff	85366990
Catalog page information	Page 46 (PC-2009)

Product notes

WEEE/RoHS-compliant since:
01/24/2006



[http://
www.download.phoenixcontact.com](http://www.download.phoenixcontact.com)
Please note that the data given
here has been taken from the
online catalog. For comprehensive
information and data, please refer
to the user documentation. The
General Terms and Conditions of
Use apply to Internet downloads.

Technical data

General data

Rated current at 40°C	4 A
Rated voltage	60 V
Number of positions	5
Volume resistance	≤ 8 mΩ
Insulation resistance	≥ 100 MΩ

General characteristics

Standards/regulations	M12 connector IEC 61076-2-101
Coding	A - standard
Surge voltage category	II
Pollution degree	3
Degree of protection	IP67
Contact material	CuZn
Contact surface material	CuSnZn
Contact carrier material	PA 66
Material of grip body	PBT
Material, knurls	Plastic
Sealing material	NBR
Type of connection	Screw connection
Conductor cross section stranded min.	0.25 mm ²
Conductor cross section stranded max.	0.75 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	18
External cable diameter	3 mm ... 5.2 mm (2x)
Status display	No

Certificates / Approvals




Certification

GOST


Diagrams/Drawings

Dimensioned drawing




M12 x 1 male connector, straight

Schematic diagram




Male/Female M12



Cable connection side M12 (screw connection)

Pin assignment M12 male connector, 5-pos., A-coded, male side



Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;