


	DIN 7500			450-550 HV
---	----------	--	--	------------



1) Tapered thread end max. 4P
2) Trilobular

BN 2723

Pozi cheese head thread forming screws

form Z, metric thread

Steel case-hardened 450-550 HV

zinc plated blue, waxed

- ~UNI 8112



ISO 4042

Quenched and tempered fasteners ≥ 360 HV and tempered case-hardened fasteners with electroplated coatings: Susceptible to hydrogen embrittlement!
Further notice to residual risks can be found in the introduction section.



Application: steel, aluminum, aluminum die-casting, zinc, zinc die-casting, non ferrous materials.
A technical brochure is available on request.

Article#	d ₁	d ₂ max.	k max.		m~	t min.	t max.	L
1371517	M2,5	4,5	1,9	1	2,4	1,1	1,35	6
1371525								8
1371533								10
1371541								12
1371908								16
1473514	M3	5,5	2,3	1	2,9	1,6	1,85	6
1473522								8
1473530								10
1473549								12
1371916								16
1371924								20
8175314	M3,5	6	2,7	2	3,7	1,5	1,75	8
8196591								10
1473557	M4	7	2,9	2	4,3	1,9	2,35	6
1473565								8
1473573								10
1473581								12
1371932								16
1371940								20
1371959								25
1371967	M5	8,5	3,7	2	4,7	2,3	2,75	8
1371975								10
1371983								12
1372122								16
1372149								20

1372963								25
---------	--	--	--	--	--	--	--	----

Article#	d ₁	d ₂ max.	k max.		m~	t min.	t max.	L
1373021	M6	10	4,3	3	6,3	2,5	2,97	10
1373404								12
1373714								16
1374451								20
1374575								25
1374699								30