

MPSA28, MPSA29

MPSA29 is a Preferred Device

Darlington Transistors

NPN Silicon

Features

- Pb-Free Packages are Available*

MAXIMUM RATINGS

Rating		Symbol	Value	Unit
Collector – Emitter Voltage	MPSA28 MPSA29	V_{CES}	80 100	Vdc
Collector – Base Voltage	MPSA28 MPSA29	V_{CBO}	80 100	Vdc
Emitter – Base Voltage		V_{EBO}	12	Vdc
Collector Current – Continuous		I_C	500	mA dc
Total Device Dissipation @ $T_A = 25^\circ\text{C}$ Derate above 25°C		P_D	625 5.0	mW mW/ $^\circ\text{C}$
Total Device Dissipation @ $T_C = 25^\circ\text{C}$ Derate above 25°C		P_D	1.5 12	W mW/ $^\circ\text{C}$
Operating and Storage Junction Temperature Range		T_J, T_{stg}	-55 to +150	$^\circ\text{C}$

THERMAL CHARACTERISTICS


Characteristic	Symbol	Max	Unit
Thermal Resistance, Junction-to-Ambient	$R_{\theta JA}$	200	$^\circ\text{C/W}$
Thermal Resistance, Junction-to-Case	$R_{\theta JC}$	83.3	$^\circ\text{C/W}$

Maximum ratings are those values beyond which device damage can occur. Maximum ratings applied to the device are individual stress limit values (not normal operating conditions) and are not valid simultaneously. If these limits are exceeded, device functional operation is not implied, damage may occur and reliability may be affected.




ON Semiconductor®


<http://onsemi.com>



MARKING DIAGRAM



TO-92
CASE 29-11
STYLE 1



MPSA2x = Device Code
x = 8 or 9

A = Assembly Location

Y = Year

WW = Work Week

■ = Pb-Free Package

(Note: Microdot may be in either location)

ORDERING INFORMATION

Device	Package	Shipping
MPSA28	TO-92	5,000 Units/Box
MPSA28G	TO-92 (Pb-Free)	5,000 Units/Box
MPSA28RLRP	TO-92	2,000/Ammo Pack
MPSA28RLRPG	TO-92 (Pb-Free)	2,000/Ammo Pack
MPSA29	TO-92	5,000 Units/Box
MPSA29G	TO-92 (Pb-Free)	5,000 Units/Box
MPSA29RLRP	TO-92	2,000/Ammo Pack
MPSA29RLRPG	TO-92 (Pb-Free)	2,000/Ammo Pack

*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

Preferred devices are recommended choices for future use and best overall value.

MPSA28, MPSA29

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

Characteristic		Symbol	Min	Typ	Max	Unit
OFF CHARACTERISTICS						
Collector – Emitter Breakdown Voltage ($I_C = 100\ \mu\text{Adc}$, $V_{BE} = 0$)	MPSA28 MPSA29	$V_{(BR)CES}$	80 100	– –	– –	Vdc
Collector – Base Breakdown Voltage ($I_C = 100\ \mu\text{Adc}$, $I_E = 0$)	MPSA28 MPSA29	$V_{(BR)CBO}$	80 100	– –	– –	Vdc
Emitter – Base Breakdown Voltage ($I_E = 10\ \mu\text{Adc}$, $I_C = 0$)		$V_{(BR)EBO}$	12	–	–	Vdc
Collector Cutoff Current ($V_{CB} = 60\ \text{Vdc}$, $I_E = 0$) ($V_{CB} = 80\ \text{Vdc}$, $I_E = 0$)	MPSA28 MPSA29	I_{CBO}	– –	– –	100 100	nAdc
Collector Cutoff Current ($V_{CE} = 60\ \text{Vdc}$, $V_{BE} = 0$) ($V_{CE} = 80\ \text{Vdc}$, $V_{BE} = 0$)	MPSA28 MPSA29	I_{CES}	– –	– –	500 500	nAdc
Emitter Cutoff Current ($V_{EB} = 10\ \text{Vdc}$, $I_C = 0$)		I_{EBO}	–	–	100	nAdc

ON CHARACTERISTICS (Note 1)

DC Current Gain ($I_C = 10\ \text{mAdc}$, $V_{CE} = 5.0\ \text{Vdc}$) ($I_C = 100\ \text{mAdc}$, $V_{CE} = 5.0\ \text{Vdc}$)		h_{FE}	10,000 10,000	– –	– –	–
Collector – Emitter Saturation Voltage ($I_C = 10\ \text{mAdc}$, $I_B = 0.01\ \text{mAdc}$) ($I_C = 100\ \text{mAdc}$, $I_B = 0.1\ \text{mAdc}$)		$V_{CE(sat)}$	– –	0.7 0.8	1.2 1.5	Vdc
Base – Emitter On Voltage ($I_C = 100\ \text{mAdc}$, $V_{CE} = 5.0\ \text{Vdc}$)		$V_{BE(on)}$	–	1.4	2.0	Vdc

SMALL – SIGNAL CHARACTERISTICS

Current – Gain – Bandwidth Product (Note 2) ($I_C = 10\ \text{mAdc}$, $V_{CE} = 5.0\ \text{Vdc}$, $f = 100\ \text{MHz}$)		f_T	125	200	–	MHz
Output Capacitance ($V_{CB} = 10\ \text{Vdc}$, $I_E = 0$, $f = 1.0\ \text{MHz}$)		C_{obo}	–	5.0	8.0	pF

1. Pulse Test: Pulse Width $\leq 300\ \mu\text{s}$, Duty Cycle $\leq 2.0\%$.

2. $f_T = h_{fe} \cdot f_{test}$.

MPSA28, MPSA29




Figure 1. DC Current Gain




Figure 2. "ON" Voltages




Figure 3. Temperature Coefficients




Figure 4. Collector Saturation Region




Figure 5. Active Region - Safe Operating Area






Figure 6. High Frequency Current Gain

MPSA28, MPSA29

PACKAGE DIMENSIONS

TO-92 (TO-226)
CASE 29-11
ISSUE AL



NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.
3. CONTOUR OF PACKAGE BEYOND DIMENSION R IS UNCONTROLLED.
4. LEAD DIMENSION IS UNCONTROLLED IN P AND BEYOND DIMENSION K MINIMUM.

DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.175	0.205	4.45	5.20
B	0.170	0.210	4.32	5.33
C	0.125	0.165	3.18	4.19
D	0.016	0.021	0.407	0.533
G	0.045	0.055	1.15	1.39
H	0.095	0.105	2.42	2.66
J	0.015	0.020	0.39	0.50
K	0.500	---	12.70	---
L	0.250	---	6.35	---
N	0.080	0.105	2.04	2.66
P	---	0.100	---	2.54
R	0.115	---	2.93	---
V	0.135	---	3.43	---

STYLE 1:

1. PIN 1. EMITTER
2. BASE
3. COLLECTOR

ON Semiconductor and  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor
P.O. Box 61312, Phoenix, Arizona 85082-1312 USA
Phone: 480-829-7710 or 800-344-3860 Toll Free USA/Canada
Fax: 480-829-7709 or 800-344-3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free
USA/Canada

Japan: ON Semiconductor, Japan Customer Focus Center
2-9-1 Kamimeguro, Meguro-ku, Tokyo, Japan 153-0051
Phone: 81-3-5773-3850

ON Semiconductor Website: <http://onsemi.com>

Order Literature: <http://www.onsemi.com/litorder>

For additional information, please contact your
local Sales Representative.