


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. DIMENSIONAL TOLERANCES:
 .XX ±.02 (.5)
 .XXX ±.01 (.25)
2. USE WITH STD, LH & HVY CROSS
 SECTION MLT's.
3. DIMS IN () ARE mm.
4. MAXIMUM SCREW HEAD HEIGHT .09 (2.3).
5. STAINLESS STEEL SCREWS ARE
 RECOMMENDED TO AVOID CORROSION
 PROBLEMS ASSOCIATED WITH
 DISSIMILAR METALS.
6. PACKAGE QTY: Q = 25

S41074_02

										PANDUIT CORP. TINLEY PARK, ILLINOIS	
										2-WAY METAL TIE MOUNT MTM2H	
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ± ANGLES ±	
										UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
02	8/04	JAMB	JJB	NOTE 2:ADDED THE "LH"(LIGHT-HEAVY)MLT PRODUCT FOR USE WITH MTM2H TIE MOUNT	I1906	CCH	JJB	DRAWN BY BJO	MAT'L: 304 STAINLESS STEEL		SCALE 2X
01	1/01	KMD	JAC	ADDED NOTE 6. CAD FILE SPEC WAS N41074SA_PCD_00	O9010	CCH	JAC	DATE 11/11/92			DRAWING NO. S41074
00	11/92	BO	JAC	RELEASED	01265	GP	LCA	CHK'D JAC			DWG A SIZE
REV	DATE	BY	CHK	DESCRIPTION	ECN #	PM	CUST				