








FCIconnect.com

Copyright FCI



Part Number & Date Code Printing

PC card drilling dimensions(after plating)
(thickness 1.60±0.20mm)



PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	200 Mating cycles	500 Mating cycles
09	30.81	24.99	16.96	16.21	10.96	D09S33E4GX00**	D09S33E6GX00**
15	39.14	33.32	25.18	24.54	19.18	D15S33E4GX00**	D15S33E6GX00**
25	53.03	47.04	39.12	38.25	33.12	D25S33E4GX00**	D25S33E6GX00**
37	69.32	63.50	55.68	54.71	49.68	D37S33E4GX00**	D37S33E6GX00**

LF FOR LEAD FREE

GENERAL CHARACTERISTICS : SEE DRAWING C01-8646-0000

mat'l. code				surface	tolerance	projection	product family			
-				ISO 1302	ISO 406 ISO 1101		D-SUB			
ltr	ecn no	dr	date	tolerances unless otherwise specified			title			
D	ELX-I-19243	AB	2014-10-29	angles	linear		SOCKET CONNECT. DELTA-D R/A			
				0°±2'			WITH NUT, HARPOON & METAL PLATE			
				dr	JOHN SLEEBA	1994-10-14	dwg no		sheet 1 of 1	size
				enr	ALIAS BABU	2014-10-29	C01-8646-0823			A3
				chr	MITHUN PAUL	2014-10-29	type Product Customer Drawing			
				app	BIJU K PAUL	2014-10-29				
sheet index	revision	D	1							
	sheet									