




Notes:

1. Material: Copper tubing PCC022, per Panduit Material Specification T-MS-6.
2. Plating: Electro tin plate 200 micro inches minimum over all internal and external surfaces.
3. Parts to be free from burrs, .015 max, excessive scratches and indentations.
4. Ink mark barrel per Panduit drawing N01124FY .
5. Barrel marking shall be located so that the "PANDUIT" is located atop the barrel O.D. as shown in the Markings Location Detail.



SECTION A-A
SCALE 2 : 1

Part Weight: 0.0221 lb
Mat'l Allocation Weight: 0.0318 lb
Plating Area: 2.8901 sq. in.
Pounds per Tote: 15.5
Plating Half Barrel Quantity: 700
Box Quantity: 50
Box: PBX433
Label: TT33GBWA
Stuffer: T-PMPI-63-PC

Cut Length: 2.600+/- .004

									PANDUIT CORP. TINLEY PARK, ILLINOIS					
									LCD6-14J-L Product Control Drawing					
									UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ± ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION			
									DRAWN BY DRL	MAT'L: SEE NOTE 1 ABOVE		SCALE 2:1		
01	9/07	JHNU	JHNU	REMOVED NAVY NUMBER FROM STAMP								DATE 4/22/02	DRAWING NO / CAD FILE LCD6-14J-PCD	DWG B SIZE
REV	DATE	BY	CHK	DESCRIPTION				ECN	CUST			QA	APP	CHK'D