


POSITIVE ADJUSTABLE VOLTAGE REGULATOR

IP117MH / LM117H
IP117MAH
IP117MHVH / LM117HVH
IP117MAHVH



FEATURES

- 1% Output Voltage Tolerance Guaranteed (A Version)
- 0.3% Load Regulation Guaranteed
- 0.01% Line Regulation Guaranteed
- 0.5A Output Current Guaranteed
- Internal Thermal Overload Protection
- Output Short Circuit Protected
- Hermetic Metal TO39 (TO-205AF) Package
- Screening Options Available

APPLICATIONS

- Adjustable Power Supplies
- System Power Supplies
- Precision Voltage / Current Regulators

DESCRIPTION

The 117M Series regulators are adjustable 3 terminal voltage regulators capable of supplying in excess of 0.5A over an output voltage range of 1.25V to 40V (HV Series, 60V). The regulators are exceptionally easy to apply requiring only 2 external resistors to set the output voltage.

Every effort has been made to make these devices easy to use and difficult to damage. Internal current limiting and power limiting coupled with true thermal limiting prevents damage due to overloads or shorts.

ABSOLUTE MAXIMUM RATINGS ($T_C = 25^\circ\text{C}$ unless otherwise stated)

$V_I - V_O$	Input – Output Voltage Differential	Standard	40V
		HV Series	60V
I_O	Output Current	Internally Limited	
P_D	Power Dissipation	Internally Limited	
T_J	Operating Junction Temperature Range	-55 to +150°C	
T_{stg}	Storage Temperature Range	-65 to +150°C	

THERMAL PROPERTIES

Symbols	Parameters	Min.	Typ.	Max.	Units
$R_{\theta JC}$	Thermal Resistance, Junction To Case			15	°C/W

Semelab Limited reserves the right to change test conditions, parameter limits and package dimensions without notice. Information furnished by Semelab is believed to be both accurate and reliable at the time of going to press. However Semelab assumes no responsibility for any errors or omissions discovered in its use. Semelab encourages customers to verify that datasheets are current before placing orders.

The diagram shows an IP117 precision current source circuit. The IP117 IC is connected to an input voltage V_{IN} at its ADJ pin. The output of the IP117, V_{OUT} , is connected to the non-inverting input of an LM301A op-amp. The LM301A is configured as a voltage follower with a feedback resistor of $1k\Omega$ and a compensation capacitor of $5\mu F$. The output of the LM301A is connected to the output of the IP117. The output current I_{OUT} is determined by the load resistor R_L and the output voltage V_{OUT} . The circuit is powered by a $5V$ supply and a $25V$ supply.

The circuit diagram shows a 5V TTL level shifter. It consists of an IP117 voltage divider, a 2N3904 transistor, and several resistors and capacitors. The input V_{IN} is connected to the V_{IN} pin of the IP117. The output V_{OUT} is connected to the V_{OUT} pin of the IP117. The IP117 is configured with a $1\mu F$ capacitor and a $1k\Omega$ resistor. The output V_{OUT} is connected to a 121Ω resistor and a 383Ω resistor. The transistor 2N3904 is connected with its base to the V_{OUT} pin of the IP117 and its emitter to ground. The collector of the transistor is connected to the V_{OUT} pin of the IP117 and the 383Ω resistor. The output V_{OUT} is connected to the $5V_{OUT}$ pin of the IP117.

[illegible]

C1 improves ripple rejection
 X_c should be small compared to R_2


The circuit diagram shows a precision current source. An input voltage V_{IN} is connected to the non-inverting input of an IP117 precision centrabuck converter. The output of the IP117, V_{OUT} , is connected to the base of a 2N3906 NPN transistor. The emitter of the transistor is connected to ground. The collector of the transistor is connected to a 10k Ω resistor, which is in series with a 20k Ω resistor connected to ground. A 243 Ω resistor is connected between the V_{OUT} pin and the collector of the transistor. A 50 Ω resistor is connected between the ADJ pin of the IP117 and the collector of the transistor. A thermally coupled diode is connected between the collector of the transistor and the ADJ pin of the IP117. A 12V battery is connected to the collector of the transistor through a 50k Ω resistor.

Temperature Compensated Lead-Acid Battery Charger

POSITIVE ADJUSTABLE VOLTAGE REGULATOR

MECHANICAL DATA

Dimensions in mm (inches)



Low Profile TO39 (TO-205AF)

H Package
Underside View

Pin 1 = V_{IN} Pin 2 = ADJ Pin 3 = V_{OUT}