




MATERIAL NUMBER	OLD PART NUMBER	FINISHED LENGTH	MATERIAL CABLE	CABLE COLOR
1201140067	BTY801P-FBE-02	6.56' +3.50" -0 [2.0M +88.9 -0]	PVC	YELLOW
1201140068	BTY801P-FBE-05	16.40' +6.50" -0 [5.0M +165.1 -0]	PVC	YELLOW
1201140069	BTY801P-FBE-10	32.81' +12.50" -0 [10.0M +317.5 -0]	PVC	YELLOW
1201140070	BTY801P-FBE-15	49.21' +24.50" -0 [15.0M +622.3 -0]	PVC	YELLOW
1201140071	BTY801P-FBE-20	65.62' +24.50" -0 [20.0M +622.3 -0]	PVC	YELLOW
1201140072	BTY801P-FBP-05	16.40' +6.50" -0 [5.0M +165.1 -0]	PUR	BLACK
1201140073	BTY801P-FBP-10	32.81' +12.50" -0 [10.0M +317.5 -0]	PUR	BLACK
1201140074	BTY801P-FBP-15	49.21' +24.50" -0 [15.0M +622.3 -0]	PUR	BLACK
1201140075	BTY801P-FBP-20	65.62' +24.50" -0 [20.0M +622.3 -0]	PUR	BLACK
1201140076	BTY801P-FBP-25	82.02' +24.50" -0 [25.0M +622.3 -0]	PUR	BLACK
1201140077	BTY801P-FBP-30	98.43' +24.50" -0 [30.0M +622.3 -0]	PUR	BLACK
1201140078	BTY801P-FBP-50	164.04' +24.50" -0 [50.0M +622.3 -0]	PUR	BLACK



ITEM	COMPONENT	MATERIAL	FINISH
1	INSERT	NYLON	BLACK
2	CONTACT SOCKET	COPPER ALLOY	GOLD OVER NICKEL
3	O-RING	VITON	RED
4	RECEPTACLE SHELL	BRASS	NICKEL PLATED
5	HOUSING	PBT	YELLOW
6	LABEL	ABS	WHITE
7	LENS	NYLON	CLEAR
8	CABLE, 18AWG, 3 CONDUCTOR, 22AWG, 8 CONDUCTOR, 300V	SEE TABLE	SEE TABLE

ADD 2 PINS TO TABLE

EC NO: WEU2010-0441

DRWN: BBRAUCH 16.03.10

CH'KD: BWOODMAN

APPR: FPACHER 2010/03/19

B

DESCRIPTION

REV

QUALITY SYMBOL

$\nabla=0$

$\sphericalangle=0$

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	$\pm---$	$\pm---$
3 PLACES	$\pm---$	$\pm---$
2 PLACES	$\pm---$	$\pm.01$
1 PLACE	± 0.3	$\pm---$
ANGULAR $\pm---$ °		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		

DIMENSION STYLE

IN/MM

DRAWN BY	DATE
LHARTMAN	2009/08/24
CHECKED BY	DATE
BWOODMAN	2009/08/26
APPROVED BY	DATE
FPACHER	2010/03/18
MATERIAL NO.	SEE CHART
SIZE	C

SCALE

NTS

TITLE

MICRO-CHANGE MPIS 8 PORT TOP MOUNT PNP #18/3 + #22/8 CABLE

MOLEX INCORPORATED

SD-120114-006

1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DESIGN UNITS

METRIC

THIRD ANGLE PROJECTION

VOLTAGE RATING	10-30 VDC
AMPERAGE RATING PER PORT	4 AMPS
PROTECTION	IP67
OPERATING TEMPERATURE	-20°C TO 90°C
UL CERTIFICATIONS	UL RECOGNIZED, FILE NO. E46237
CSA CERTIFICATIONS	CSA CERTIFIED, FILE NO. LR6837