

DATASHEET (ADDENDUM)

High Temperature Operation (125°C)

This data sheet addendum is to be used in conjunction with the existing AT25SF041 datasheet specifications. The Adesto AT25SF041 4Mbit Serial Flash devices will operate @ 125°C with the following datasheet caveats. All other parameters will meet the existing datasheet specifications.

The ordering code suffix (CAN# Code) 'HR' or 'HT' must be used to ensure correct operation at this extended temperature range. Adesto will not modify and republish the current datasheet to reflect the CAN# 'HR' or 'HT' ordering code or the above caveats. The standard [AT25SF041 datasheet](http://www.adestotech.com) is available at <http://www.adestotech.com>.

1. Electrical Specifications

1.1 DC and AC Operating Range

		AT25SF041-xxxHR
Operating Temperature		-40°C to +125°C
Endurance (Maximum)		10,000 Cycles

1.2 DC Characteristics

Symbol	Parameter	Condition	2.5V to 3.6V			Units
			Min	Typ	Max	
I _{DDP}	Deep Power-Down Current	$\overline{CS}, \overline{HOLD}, \overline{WP} = V_{IH}$			10 ⁽¹⁾	μA
I _{SB}	Standby Current	$\overline{CS}, \overline{HOLD}, \overline{WP} = V_{IH}$			35 ⁽²⁾	μA

1. Industrial temperature limit is 5μA.

2. Industrial temperature limit is 25μA.

1.3 Program and Erase Characteristics

Symbol	Parameter	2.5V to 3.6V			
		Min	Typ	Max	Units
$t_{PP}^{(1)}$	Page Program Time (256 Bytes)		0.7	3.5	ms
$t_{CHPE}^{(1)(2)}$	Chip Erase Time		4	12	sec

1. Maximum values indicate worst-case performance after 100,000 erase/program cycles.
2. Not 100% tested (value guaranteed by design and characterization).

2. Ordering Code

2.1 Ordering Code Detail

Ordering Code ⁽¹⁾	Package	Operating Voltage	Max. Freq. (MHz)	Operation Range
AT25SF041-SHDHR-T	8S2	2.5V to 3.6V	85MHz	Extended (-40°C to +125°C)
AT25SF041-SHDHR-B				
AT25SF041-SSHDHR-T	8S1			
AT25SF041-SSHDHR-B				
AT25SF041-DWFHT ⁽²⁾	DWF			

1. The shipping carrier option code is not marked on the devices.
2. Contact Adesto for mechanical drawing or die sales information.

Package Type	
8S1	8-lead, 0.150" Wide, Plastic Gull Wing Small Outline Package (JEDEC SOIC)
8S2	8-lead, 0.208" Wide, Plastic Gull Wing Small Outline Package (EIAJ SOIC)
DWF	Die in Wafer Form

3. Revision History

Revision Level – Release Date	History
A – August 2014	Initial release.
B – October 2015	Corrected package type in Ordering Code Detail table.
C – August 2016	Added DWF part ordering code.
D – August 2017	Updated corporate address information.



Corporate Office

California | USA

Adesto Headquarters

3600 Peterson Way

Santa Clara, CA 95054

Phone: (+1) 408.400.0578

Email: contact@adestotech.com

© 2017 Adesto Technologies. All rights reserved. / Rev.: DS-25SF041–050D–8/2017

Disclaimer: Adesto Technologies Corporation makes no warranty for the use of its products, other than those expressly contained in the Company's standard warranty which is detailed in Adesto's Terms and Conditions located on the Company's web site. The Company assumes no responsibility for any errors which may appear in this document, reserves the right to change devices or specifications detailed herein at any time without notice, and does not make any commitment to update the information contained herein. No licenses to patents or other intellectual property of Adesto are granted by the Company in connection with the sale of Adesto products, expressly or by implication. Adesto's products are not authorized for use as critical components in life support devices or systems.