





REV.	DATE	DESCRIPTION
A	09/01/98	MODIFY CONTACT I.D.
B	06/05/03	UPDATE DRAWING FORMAT



NOTE:

1. CRIMPED FERRULE
HEX CRIMP SIZE .213"
2. CRIMPED CONTACT PIN
HEX CRIMP SIZE .068"

8				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	Amphenol Connex TNC CRIMP JACK – REVERSE POLARIZED RG58/U CABLE PART NO. 122122RP
7				UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:	DRAWN	G.R.S.	
6				0.5 – 8mm ± 0.20mm	CHECKED		
5				8 – 30mm ± 0.40mm	ISSUED		
4	FERRULE	COPPER	NICKEL	30 – 120mm ± 0.50mm			
3	INSULATOR	TEFLON	NATURAL	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:			PART NO. 122122RP
2	CONTACT PIN	BRASS	GOLD	.020 – .315 = ± 0.007"	SHEET	1 OF 1	
1	BODY	BRASS	NICKEL	.315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"			
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	CAD FILE C:/122/122122RP.DWG	DWG. NO. 122122RP.DWG REV. NC SIZE A SCALE NA