

C-TYPE INSERT & EXTRACT DRIVER TOOLS RS STOCK NO: 423-927

MATERIAL: CHROME VANADIUM STEEL

FOR NUT END, MEDIUM CARBON STEEL

FOR BLADES AND FOR END INSERT

SCREW AND EXTRUSION CELLULOSE ACETATE

HANDLES.

FINISH: CHROME PLATED FINISH NUT END,

BLADE & END INSERT AND RED COLOR HANDLE.

CONTENTS:

1 PC - 300 MM C-TYPE BNC / TNC INSERT

& REMOVAL TOOLS FOR EASY ACCESS

TO LOCATION OF COAXIAL CONNECTOR

WITH ACETATE HANDLE.

(OVERALL LENGTH - 410 MM,

BLADE LENGTH - 300 MM

SPECIFICATION:

1. NUT END-ACROSS FLAT DIMENSION-11.12 MM

OUTSIDE DIMENSION - 17.5 MM (MAXIMUM),

ACROSS WIDTH FOR C-CUT GROOVE-7.11~8.48M

2. END INSERT SCREW-OUTSIDE DIAMETER-7.5M

EXTENDED LENGTH - 14.5 ~17.5MM

PITCH- 3/8-32NF2 AND CENTRAL HOLE

DIAMETER - 2.54 MM (MINIMUM)