

10 9 8 7 6 5 4 3 2 84525


F STRIP MATERIAL NUMBER

84525-0025 SELECTIVE TIN 100 μ INCH MINIMUM OVER NICKEL 80 μ INCH MINIMUM OVERALL

84525-0046 SELECTIVE HARD GOLD 30 μ INCH MINIMUM WITH SELECTIVE TIN 100 μ INCH MINIMUM OVER NICKEL 50 μ INCH MINIMUM OVERALL

F FINISH

PAYOFF DIRECTION



WIRE INSULATION O.D. RANGE .095-.150
2.41-3.81

NOTES:

1. TERMINAL MATERIAL: COPPER ALLOY, .0118/0.300 THICK. FINISH: SEE CHART.
2. HOOD MATERIAL: STAINLESS STEEL, .006/0.15 THICK.
3. STRIP PARTS ARE REELED 3000 PARTS PER REEL AS SHOWN ABOVE.
4. TERMINAL FOR USE WITH SERIES XRC CONNECTOR ASSEMBLIES.
5. ALL MATERIALS AND FINISHES ARE ROHS COMPLIANT.

UPDATE LENGTH	EC NO: IPG2012-0063	2011/12/06	DRAWN/WLEUNG	CHKD: APPR:DITIUS	2012/01/09	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE IN/MM	SCALE 2:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION
D						▼=0	4 PLACES \pm --- \pm ---	mm INCH	DRAWN BY MODELL	DATE 2009/04/09	
						▼=0	3 PLACES \pm --- \pm .005		CHECKED BY	DATE	
							2 PLACES \pm .13 \pm ---		APPROVED BY	DATE	
							1 PLACE \pm --- \pm ---		DTITUS	2010/12/06	molex MOLEX INCORPORATED
							ANGULAR \pm ---°		MATERIAL NO.	DOCUMENT NO.	
							DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART	SD-84525-007	SHEET NO. 1 OF 1

SIZE B THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION