



THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO POSITRONIC AND IS SUBMITTED FOR INFORMATION ONLY. THE USER EMPLOYER'S TECHNICAL INFORMATION IS GIVEN FREE OF CHARGE. THE USER EMPLOYER'S TECHNICAL INFORMATION AT HIS OWN DISCRETION. POSITRONIC ASSUMES NO LIABILITY FOR THE USE OF SUCH INFORMATION IN WHOLE OR IN PART.

SK10946

DATE	REV	REVISION/RECORD	APP	DR	CK
8-12-09	NC	ECO 31419	RCW	BS	TK



NOTES:

1. MATERIALS AND FINISHES:

- INSULATOR: GLASS FILLED POLYESTER PER MIL-M-24519, UL 94V-0, COLOR: BLUE.
- CONTACTS: PRECISION MACHINED COPPER ALLOY, GOLD FLASH OVER NICKEL PLATE.
- SHELLS: STEEL, ZINC PLATE WITH CHROMATE SEAL.
- SPACED SPACER: PHOSPHOR BRONZE WITH TIN PLATE.

2. ELECTRICAL CHARACTERISTICS:

- CONTACT CURRENT RATING: 5 AMPERES NOMINAL.
- INITIAL CONTACT RESISTANCE: 0.010 OHMS MAX.
- INSULATOR RESISTANCE: 5 G OHMS.
- WORKING VOLTAGE: 300 VAC [rms]
- TEMPERATURE RANGE: -55°C TO +125°C
- DIMENSIONS ARE IN INCHES [MILLIMETERS].

**POSITRONIC INDUSTRIES INC.**  
 www.connectpositronic.com  
 FSC# 28198

DECIMAL TOL. ± 0.015 [0.38]	SCALE N.T.S.	DRAWN BY B SHELLBY	DATE 8-12-09	DRAWING NUMBER SK10946	REV. NC
ANGULAR TOL. ± 5°	TITLE CBDD	APPROVED BY R WILLIAMS			