





	13	12	11	10	9	8	7	6	5	4	3	2	1	
	MATERIAL NUMBER ON STRIP	ENGINEERING NUMBER ON STRIP	MATERIAL NUMBER LOOSE PIECE	ENGINEERING NUMBER LOOSE PIECE	TAPE MATERIAL NUMBER	TAPE ENGINEERING NUMBER	AWG	TAB SIZE	D MAX					
J	190080008	AAZ-1147	190080001	AA-1147	190080004	AA-1147T	22-18	.187 X .020	.257/6.53					J
	190080009	AAZ-1147-032	190080002	AA-1147-032	190080003	AA-1147-032T	22-18	.187 X .032	.257/6.53					
	190080013	AAZ-1158	190080006	AA-1158	190080007	AA-1158T	22-18	.250 X .032	.312/7.92	(B)				
	190080028	BBZ-1148	190080019	BB-1148	190080022	BB-1148T	16-14	.187 X .020	.257/6.53					
	190080029	BBZ-1148-032	190080020	BB-1148-032	190080021	BB-1148-032T	16-14	.187 X .032	.257/6.53					
I	190080031	BBZ-1159	190080024	BB-1159	190080027	BB-1159T	16-14	.250 X .032	.312/7.92	(B)				I



SALES DRAWING

NOTES:

1. MATERIAL: BRASS .016/0.04 THICK.
PLATING ELECTRO-TIN.
2. TAB SIZE SEE CHART.
3. WIRE AWG SEE CHART.

- (B) 4. PART IS ROHS COMPLIANT.

REVISED BARREL & CHART EC NO: ETC2007-0001 DRAWN BY: 2006/07/13 CHKD: JMACNEIL APPR: RDEROSS 2006/07/17	QUALITY SYMBOLS ▽=0 ▽=0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	 THIRD ANGLE PROJECTION
					IN/MM		NONE	INCH	
					DRAWN BY DATE		TITLE		
					BENDERLE 2005/01/25		FLAG QD		
B	REV	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	mm INCH		CHECKED BY DATE		22-18 AWG & 16-14 AWG		
			4 PLACES ± .--- ± .---		R DEROSS 2005/01/25		.187X.020&.032,.250X.032		
			3 PLACES ± .--- ± .005		APPROVED BY DATE		MOLEX INCORPORATED		
			2 PLACES ± .13 ± .01		R DEROSS 2005/01/25		DOCUMENT NO.		
1 PLACE ± .25 ± .---		ANGULAR ±1/2°		MATERIAL NO.		SD-19008-013		SHEET NO.	
				SEE CHART				1 OF 1	
				SIZE C					