

Miniature Fuse, 6.3 x 32 mm, Quick-Acting F, GAM T1, 250 VAC, 125 VDC



250VAC · 125VDC · Quick-Acting F

See below:

Approvals and Compliances**Description**

- High breaking capacity

ReferencesCorresponding Fuseholder [231549P](#)**Weblinks**

[pdf data sheet](#), [html data sheet](#), [General Product Information](#), [Packaging details](#), [Distributor-Stock-Check](#), [Detailed request for product](#)

Technical Data

Rated Voltage	250VAC, 125VDC
Rated current	0.16 - 20A
Breaking Capacity	1 kA - 10 kA
Characteristic	Quick-Acting F
Mounting	Fuseholder / Clip
Admissible Ambient Air Temp.	-40 °C to 125 °C
Climatic Category	40/125/56 acc. to IEC 60068-1
Material: Tube	Ceramic
Unit Weight	3 g
Storage Conditions	0 °C to 60 °C, max. 70% r.h.
Product Marking	 , Rated current, Rated Voltage, HA39

Resistance to Vibration	acc. to NF C 20-706 / IEC 60068-2-6, test Fc
Shocks	acc. to NF C 20-706 / IEC 60068-2-27
Bumps	acc. to NF C 20-729 / IEC 60068-2-29
Salt Mist	acc. to NF C 20-711 / IEC 60068-2-11

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in [Details about Approvals](#)

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

Approvals

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products.

Approval Reference Type:

Approval Logo	Certificates	Certification Body	Description
GAM T1			
NNO			

Application standards

Application standards where the product can be used

Organization	Design	Standard	Description
	Designed for applications acc.	IEC/UL 60950	IEC 60950-1 includes the basic requirements for the safety of information technology equipment.


Compliances

The product complies with following Guide Lines

Identification	Details	Initiator	Description
CE	CE declaration of conformity	SCHURTER AG	The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008.
	RoHS	SCHURTER AG	EU Directive RoHS 2011/65/EU
	China RoHS	SCHURTER AG	The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.
	REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.

Dimension [mm]

32 mm




Pre-Arcing Time

Rated Current In 1.1 x In min. 1.7 x In max. 3.0 x In max.

0.16 A - 20 A	60 min	60 min	10 s
---------------	--------	--------	------

Time-Current-Curves



All Variants

Rated Current [A]	Rated Voltage [VAC]	Rated Voltage [VDC]	Breaking Capacity	Voltage Drop 1.0 I _n typ. [mV]	Power Dissipation 1.1 I _n typ. [mW]	Melting I _{st} 10.0 I _n typ. [A ² s]	GAM T1 NNO	Order Number
0.16	250	125	1)	3000	770	0.0021	●	7023.0790
0.25	250	125	1)	2290	870	0.0075	●	7023.0810
0.4	250	125	1)	1800	1000	0.01	●	7023.0830
0.63	250	125	1)	1050	1050	0.44	● ●	7023.0850
1	250	125	1)	770	1170	0.16	●	7023.0870
1.6	250	125	1)	540	1350	0.74	● ●	7023.0890
4	250	125	1)	220	1300	24	●	7023.0930
6.3	250	125	1)	310	3100	27	●	7023.0950
8	250	125	1)	90	1050	9.3	●	7023.0960
10	250	125	1)	85	1350	34	● ●	7023.0970
12.5	250	125	1)	90	1600	62		7023.0980
16	250	125	1)	80	1900	160		7023.0990
20	250	125	1)	75	2000	240		7023.0940

■ Most Popular.

Availability for all products can be searched real-time: <https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

1) 10 kA @ 250 VAC , p.f. = 0.7 - 0.8 / 1 kA @ 125 VDC

Packaging Unit Small Box Pack (10 pcs.)