







SECTION A-A



SECTION B-B



DIMA PER C.S. spess.1.5 ±0.1
VISTA LATO COMPONENTI
RECOMMENDED PCB LAYOUT, PCB THICK: 1.5 ±0.1
VIEW FROM COMPONENT SIDE



CODICE	P/N	MATERIALE
94529-9102		PA 66 NAT. UL94 V2 GWT 850 °C
94529-7102		PA 66 NAT. UL94 V0
94529-4102		NYLON 6.6 GWT 750 °C sec. IEC 60335-1 TEST METHOD IEC 60695-2-11 NATURAL

NOTA: LE DIMENSIONI VANNO MISURATE CON CORPI
STABILIZZATI SECONDO NG 2301.
(AUMENTO IN PESO DEL 2.7 %)

NOTE: PARTS SHALL BE DIMENSIONALLY CHECKED AFTER
ATTAINING EQUILIBRIUM CONDITIONS E.G. 2.7 % INCREASE
IN WEIGHT FOR HUMIDITY ABSORPTION FROM DRY STATUS.

CARATTERISTICHE PRODOTTO SECONDO PS-94529
PRODUCT CHARACTERISTICS ACCORDING TO PS-94529 E

CONFEZIONE: 4500 pz. in scatola
PACKAGING: 4500 pcs. in carton box

SPQ: 4500 pz.

Descr.Std: HSG FOR FORK TERMINAL 2 CKT

EC NO: Z2006-0051 DRWN:FGOTTARD2005/10/12 CHKD:RSANDAN02005/10/12 APPR:GZUIN 2005/10/14	DESCRIPTION	QUALITY SYMBOLS ▽-0 ▽-0	GENERAL TOLERANCES (UNLESS SPECIFIED)		SCALE 2:1	DESIGN UNITS METRIC	FIRST ANGLE PROJECTION	REVISE ON CAD ONLY			
				mm	INCH	DIMENSION STYLE MM ONLY		TITLE 2 CKT HOUSING FOR STRAIGHT FORK TERMINAL			
			4 PLACES	± ---	± ---	DRAWN BY					DATE
			3 PLACES	± ---	± ---	FGOTTARD					2000/01/24
			2 PLACES	± 0.10	± ---	CHECKED BY		DATE	MOLEX INCORPORATED		
1 PLACE	± 0.2	± ---	MTESTAGU		2000/01/24						
			ANGULAR ± 2 °								
			DRAFT WHERE APPLICABLE		APPROVED BY		DATE	MATERIAL NO.	DOCUMENT NO.	SHEET NO.	
					RMARTUCC		2000/01/24	SEE TABLE	SD-94529-004	1 OF 1	
			MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
B3	REV										A3