






Certain electrical and control systems require protection by fuses. The terminal has a hinged carrier that has a specially designed space for a cartridge type glass fuse of size Ø5 x 20 or Ø5 x 25 mm. The fuse can be engaged or disengaged by the movement of the carrier.

Altech fuse terminals are also available with light indication - CSFL 4U (L). A specially de-signed built-in circuit gives light indication in the event of fuse blow out.

† Fuses are sold separately Altech, see pages 23-24.

*Add required voltage to part number as a suffix, i.e. CSFL4U(L)/24 for 24V DC

	CSFL4U		CSFL4U(L)*	
				
	† Fuse not included.		† Fuse not included.	
Terminal Width	8 mm		8 mm	
Height x Length	43 x 58 mm		43 x 58 mm	
Stripping Length	9.5 mm		9.5 mm	
Insulation Material	Polyamide 6.6		Polyamide 6.6	
Type of Connection	2 screw clamps		2 screw clamps	
LED Voltage			24V AC/DC, 48V AC/DC, 110V AC/DC, 220V AC, 300V AC	
Type of Fuse Used	Ø5x20, Ø5x25mm		Ø5x20, Ø5x25mm	
Approvals				
Wire Range	22-10 AWG		22-10 AWG	
Voltage Rating	600 V		600 V	
Current Rating	6.3 A		6.3 A	
Torque	7 lb-in		7 lb-in	
Other Approvals				
Terminal Block	Cat. No.	Std. Pk.	Cat. No.	Std. Pk.
	CSFL4U	100	CSFL4U(L)*	100
End Plate 	EPCSFL4U	50	EPCSFL4U	50
Isolation Partition 	PPCSFL4U	50	PPCSFL4U	50
DIN Rail for ordering information refer to page 72				
End Stop for ordering information refer to page 74 	CA602	100	CA602	100
Internal Jumper 	2 pole 3 pole 4 pole 10 pole			
Insulated Internal Jumper 	2 pole 3 pole 4 pole 10 pole			
Current Bars 	2 pole 3 pole 4 pole 10 pole 10 pole (breakable) 100 pole			
Shorting Sleeve & Screw 				
External Jumper 	2 pole 3 pole 4 pole 10 pole			
Marking Tags (MT Type) 	MT8	100	MT8	100
(MT Type on Lever)	MT2	100	MT2	100

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Altech:](#)

[CSFL4U\(L\)/24](#) [CSFL4U](#)