

# POGO PIN SINGLE CONTACT:

9150-000

## General Information



Single Pogo Pin contacts provide high cycle life in industrial and medical applications where reliability and robustness is critical. Pogo Pins provide 10,000 mating cycles and are ideal in pluggable module applications where the end customer has to handle a product daily. Pogo Pins are designed to mate with gold plated PCB pads or flat contacts in docking/cradle applications to function as the charging, data transfer or programming interface to a portable device.

The standard range single contacts from KYOCERA AVX provides the maximum flexibility in pin count, placement location and broad compressed stacking heights ranging from 2.0mm up to 5.5mm. The contacts are provided in standard tape and reel packaging for automatic in-line SMT placement. A disposable plastic cap facilitates vacuum pick-up and then is removed after reflow soldering prior to product mating. Contacts are gold plated and incorporate high force stainless steel springs for durability and signal integrity.

### APPLICATIONS

- Base/Docking stations for portable electronic devices to recharge batteries or download data
- Testing and programming of electronic modules
- Interface to disposable medical or measurement components
- Product Specification: Refer to 201-01-158
- Application Notes: Refer to 201-01-159

### FEATURES AND BENEFITS

- Contacts range from 1.9mm to 5.5mm providing off-the-shelf availability for almost any application
- Each contact height provides the maximum working range and compressed height tolerance possible
- Gold plated contacts provide high reliability and signal integrity over 10,000 cycles
- Removable pick-up cap facilitates automatic placement for SMT reflow

### ELECTRICAL

- Current Rating: 1 Amp
- Voltage Rating: VAC (RMS) or DC equivalent  
Based on placement distance

### ENVIRONMENTAL

- Operating Temperature: -40°C to +125°C
- Storage Temperature: -40°C to +70°C

### MECHANICAL

- Contact Material: Brass
- Contact Plating: Gold over Nickel
- Spring Material: SUS304
- Durability: 10k Cycles

### HOW TO ORDER

70      9150      001  
Prefix    Series    Number of Ways  
70 = Contact    9150 = 1

0XX  
Contact Operating Range  
020 = 1.90 to 2.30  
025 = 2.40 to 2.80  
030 = 2.90 to 3.40  
040 = 3.90 to 4.50  
050 = 4.90 to 5.50

0  
Sleeve Diameter  
0 = 1.50

0  
Packing Option  
0 = Tape & Reel

6  
Plating Option  
6 = Gold over Nickel



SALES DRAWINGS  
CLICK TO DOWNLOAD

