



+ TERMINALS & SPLICES

SPLICES



✓ Active

TE CONNECTIVITY (TE)

D-150-0177

Raychem

682035-000
TE Internal Number: 682035-000
Alias ID: 2-1195361-5

Not EU RoHS Compliant
Not EU ELV Compliant

Product Type Splice
Terminal & Splice Style Splice
Splice Type SolderShield
Wire/Cable Type Multi-Conductor
Operating Temperature Range (°C) 150

↓ PRODUCT DRAWING
English

DOCUMENTATION

Product Drawings

1 To 1 Splices-Crimp SolderShield Splice Kit, Shielded Cable
PDF
English

Catalog Pages/Data Sheets

1654025_Sec8_D-150
PDF
English

Product Specifications

Product Specification

Installation Procedure For TE Connectivity Shielded Cable Splice Kits With Mini-Seal Crimp Primary Splices

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Product Type Splice
Splice Type SolderShield
Wire/Cable Type Multi-Conductor

Configuration Features

Number of Conductors Two-conductor cable

Body Features

Plating Material Tin/Silver

Contact Features

Terminal & Splice Style Splice

Usage Conditions

Operating Temperature Range (°C) 150

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance
PDF