




- 1 24 POSITIONS LOADED WITH POSTED PIN CONTACT. POSITION 17 LOADED WITH GROUND CONTACT.
- 2 POSITIONS 1,2,4,5,7-10,12,14,20 AND 25 LOADED WITH POSTED PIN CONTACT. POSITIONS 3,6,11,13,15-19 AND 21-24 LOADED WITH GROUND CONTACT.
- 3 0.76um[.000030] MIN GOLD FOR A LENGTH OF 5.08[.200] MIN FROM MATING END, GOLD FLASH ON THE REMAINDER, BOTH OVER 1.27um [.000050] MIN NICKEL ON PIN END. POST END 2.54um[.000100] MIN TIN-LEAD OVER 2.54um[.000100] MIN COPPER.
4. CONTACT ASSEMBLY SHOULD BE FULLY SEATED IN HOUSING PRIOR TO SOLDERING TO PRINTED CIRCUIT BOARD.
- 5 0.76um[.000030] MIN GOLD FOR A LENGTH OF 5.08[.200] MIN FROM MATING END, GOLD FLASH ON THE REMAINDER, BOTH OVER 1.27um [.000050] MIN NICKEL ON PIN END. POST END 2.54um[.000100] MIN TIN OVER 2.54um[.000100] MIN COPPER.
- 6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
FT	0		B	REVISED PER 0G3B-0230-05	4/27/05	SS
			B1	REVISED PER ECO-09-021826	07JAN10	KK

6 OBSOLETE	5	2	213756-4
	5	1	213756-3
	3	2	213756-2
	3	1	213756-1
	FINISH	LOADING	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	08/17/92	Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
		CHK	8-18-92		
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
mm				RECEPTACLE ASSEMBLY, 25 POSITION, DRAWER CONNECTOR, METRIMATE	
				SIZE	
				CAGE CODE	
				DRAWING NO	
				RESTRICTED TO	
				A2 00779 C=213756	
				SCALE	
				2:1	
				SHEET	
				1 OF 1	
				REV	
				B1	