










NOTES:

1. MATERIAL : LCP, GLASS FILLED, UL 94V-0, BLACK
TERMINAL/SOLDER TAB : COPPER ALLOY
2. FINISHES: SEE TABLE
3. PRODUCT SPECIFICATION : SEE TABLE
4. PACKAGING SPECIFICATION : TAPE AND REEL
5. MATES WITH : MOLEX MICRO SATA PLUG
6. THIS PRODUCT IS COMPLIANT TO RoHS DIRECTIVE WITH THE FOLLOWING BANNED SUBSTANCES - LEAD, MERCURY, CADMIUM, HEXAVALENT CHROMIUM, POLYBROMINATED BIPHENYLS AND POLYBROMINATED DIPHENYLS ETHERS.
7. MOLEX LOGO AND CAVITY NUMBER LOCATED APPROXIMATELY AS SHOWN
8. NON FUNCTIONAL CORING MAY VARY




SEE SHEET 4 EC NO: S2009-0967 DRAWN: GMENARLY CHKD: CGOH APPR: BOKOK	QUALITY SYMBOLS ▽=0 C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
		DESCRIPTION REV	DRAWN BY GMENARLY CHECKED BY CGOH APPROVED BY BOKOK MATERIAL NO. SEE TABLE	DATE 2009/03/17 2009/05/20 2009/05/20	TITLE MICRO SATA RECEPTACLE VERTICAL SMT 1.8 INCH SSD/HDD MOLEX INCORPORATED	DOCUMENT NO. SD-78492-001	SHEET NO. 1 OF 4		




SEE SHEET 4 EC NO: S2009-0967 DRWN:GMENARLY CHKD:CGOH APPR:BOKOK A1	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ◻=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION 				
				mm	INCH	DRAWN BY GMENARLY	DATE 2009/03/17	TITLE MICRO SATA RECEPTACLE VERTICAL SMT 1.8 INCH SSD/HDD						
			4 PLACES	± ---	± ---	CHECKED BY CGOH	DATE 2009/05/20							
			3 PLACES	± ---	± ---	APPROVED BY BOKOK	DATE 2009/05/20	MOLEX MOLEX INCORPORATED						
			2 PLACES	± 0.20	± ---	MATERIAL NO. SEE TABLE	DOCUMENT NO. SD-78492-001						SHEET NO. 2 OF 4	
			1 PLACE	± ---	± ---									
			ANGULAR ± 3 °											
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS											
			SIZE A3			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								

	10	9	8	7	6	5	4	3	2	1	
F	PART NUMBER		FINISHES					PRODUCT SPECIFICATIONS			
	78492-0001		TERMINAL CONTACT :0.127μm MIN. SELECTIVE GOLD OVER 1.27μm MIN. NICKEL UNDERPLATE TERMINAL SOLDER TAIL :2.54μm MIN. TIN OVER 1.27μm MIN. NICKEL UNDERPLATE SOLDER TAB : 2.54μm MIN. TIN OVER 1.91μm MIN. NICKEL UNDERPLATE					PS-78492-001			
	78492-0002		TERMINAL CONTACT :0.38μm MIN. SELECTIVE GOLD OVER 1.27μm MIN. NICKEL UNDERPLATE TERMINAL SOLDER TAIL :2.54μm MIN. TIN OVER 1.27μm MIN. NICKEL UNDERPLATE SOLDER TAB : 2.54μm MIN. TIN OVER 1.91μm MIN. NICKEL UNDERPLATE					PS-78492-002			
	78492-0003		TERMINAL CONTACT :0.76μm MIN. SELECTIVE GOLD OVER 1.27μm MIN. NICKEL UNDERPLATE TERMINAL SOLDER TAIL :2.54μm MIN. TIN OVER 1.27μm MIN. NICKEL UNDERPLATE SOLDER TAB : 2.54μm MIN. TIN OVER 1.91μm MIN. NICKEL UNDERPLATE								




SEE SHEET 4 EC NO: S2009-0967 DRAWN:GMENARLY CHKD:CGOH APPR:BOKOK A1	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
					DRAWN BY GMENARLY	DATE 2009/03/17	TITLE MICRO SATA RECEPTACLE VERTICAL SMT 1.8 INCH SSD/HDD				
					CHECKED BY CGOH	DATE 2009/05/20					
					APPROVED BY BOKOK	DATE 2009/05/20	MOLEX INCORPORATED				
					ANGULAR ± 3 °						MATERIAL NO.
					DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-78492-001		3 OF 4
							SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			

PACKAGING INFORMATION




NOTES:

1. LEADER AND TRAILER TAPE



2. PEELING OFF FORCE OF THE TOP TAPE: 20 - 80gf. (PEELING DIRECTION AS SHOWN IN FOLLOWING FIGURE)



3. TAPE AND REEL SPECIFICATION IS AS PER EIA-481.

4. TAPE AND REEL QUANTITY : 550 PCS/ REEL.

5. THE TAPE IS TREATED FOR ANTI-STATIC.

REV. CARRIER TAPE EC NO: S2009-0967 DRWN:GMENARLY CHKD:CGOH APPR:BOKOK A1	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ◇=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
					DRAWN BY GMENARLY	DATE 2009/03/17	TITLE MICRO SATA RECEPTACLE VERTICAL SMT 1.8 INCH SSD/HDD				
					CHECKED BY CGOH	DATE 2009/05/20					
					APPROVED BY BOKOK	DATE 2009/05/20	MOLEX INCORPORATED				
			ANGULAR ± 3 °		MATERIAL NO.						
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-78492-001			4 OF 4	

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
---	--	--	--	--	--	--	--	--	--