


Rectifier diodes Schottky barrier

PBYR2045CTF, PBYR2045CTX series

FEATURES

- Low forward volt drop
- Fast switching
- Reverse surge capability
- High thermal cycling performance
- Isolated mounting tab

SYMBOL



QUICK REFERENCE DATA

$$V_R = 40 \text{ V/} 45 \text{ V}$$

$$I_{O(AV)} = 20 \text{ A}$$

$$V_F \leq 0.57 \text{ V}$$

GENERAL DESCRIPTION


Dual, common cathode schottky rectifier diodes in a plastic envelope with electrically isolated mounting tab. Intended for use as output rectifiers in low voltage, high frequency switched mode power supplies.

The PBYR2045CTF series is supplied in the SOT186 package.
The PBYR2045CTX series is supplied in the SOT186A package.


PINNING

PIN	DESCRIPTION
1	anode 1 (a)
2	cathode (k)
3	anode 2 (a)
tab	isolated

SOT186



SOT186A



LIMITING VALUES

Limiting values in accordance with the Absolute Maximum System (IEC 134)

SYMBOL	PARAMETER	CONDITIONS	MIN.	MAX.	UNIT
V_{RRM}	Peak repetitive reverse voltage	PBYR20 PBYR20	-	40CTF 40CTX	V
V_{RWM}	Working peak reverse voltage		-	40	V
V_R	Continuous reverse voltage	$T_{hs} \leq 84 \text{ }^\circ\text{C}$	-	40	V
$I_{O(AV)}$	Average rectified output current (both diodes conducting)	square wave; $\delta = 0.5$; $T_{hs} \leq 78 \text{ }^\circ\text{C}$	-	20	A
I_{FRM}	Repetitive peak forward current per diode	square wave; $\delta = 0.5$; $T_{hs} \leq 78 \text{ }^\circ\text{C}$	-	20	A
I_{FSM}	Non-repetitive peak forward current per diode	$t = 10 \text{ ms}$ $t = 8.3 \text{ ms}$ sinusoidal; $T_j = 125 \text{ }^\circ\text{C}$ prior to surge; with reapplied $V_{RRM(max)}$ pulse width and repetition rate limited by $T_{j\max}$	-	100 110	A
I_{RRM}	Peak repetitive reverse surge current per diode		-	1	A
T_j	Operating junction temperature		-	150	$^\circ\text{C}$
T_{stg}	Storage temperature		-65	175	$^\circ\text{C}$

Rectifier diodes
Schottky barrier

PBYR2045CTF, PBYR2045CTX series

ISOLATION LIMITING VALUE & CHARACTERISTIC $T_{hs} = 25^\circ\text{C}$ unless otherwise specified

SYMBOL	PARAMETER	CONDITIONS	MIN.	TYP.	MAX.	UNIT
V_{isol}	Peak isolation voltage from all terminals to external heatsink	SOT186 package; R.H. $\leq 65\%$; clean and dustfree	-	-	1500	V
V_{isol}	R.M.S. isolation voltage from all terminals to external heatsink	SOT186A package; $f = 50\text{-}60\text{ Hz}$; sinusoidal waveform; R.H. $\leq 65\%$; clean and dustfree	-	-	2500	V
C_{isol}	Capacitance from pin 2 to external heatsink	$f = 1\text{ MHz}$	-	10	-	pF

THERMAL RESISTANCES

SYMBOL	PARAMETER	CONDITIONS	MIN.	TYP.	MAX.	UNIT
$R_{th j-hs}$	Thermal resistance junction to heatsink	per diode both diodes (with heatsink compound)	-	-	6 5	K/W K/W
$R_{th j-a}$	Thermal resistance junction to ambient	in free air	-	55	-	K/W

ELECTRICAL CHARACTERISTICS $T_j = 25^\circ\text{C}$ unless otherwise specified

SYMBOL	PARAMETER	CONDITIONS	MIN.	TYP.	MAX.	UNIT
V_F	Forward voltage	$I_F = 10\text{ A}; T_j = 125^\circ\text{C}$ $I_F = 20\text{ A}; T_j = 125^\circ\text{C}$ $I_F = 20\text{ A}$	- - -	0.45 0.64 0.64	0.57 0.72 0.84	V
I_R	Reverse current	$V_R = V_{RWM}$	-	0.3	1.3	mA
C_d	Junction capacitance	$V_R = V_{RWM}; T_j = 100^\circ\text{C}$ $V_R = 5\text{ V}; f = 1\text{ MHz}, T_j = 25^\circ\text{C to } 125^\circ\text{C}$	-	22 380	35 -	mA pF

Rectifier diodes Schottky barrier

PBYR2045CTF, PBYR2045CTX series




Fig.1. Maximum forward dissipation $P_F = f(I_{F(AV)})$ per diode; square current waveform where $I_{F(AV)} = I_{F(RMS)} \times \sqrt{D}$.




Fig.4. Typical reverse leakage current per diode; $I_R = f(V_R)$; parameter T_j




Fig.2. Maximum forward dissipation $P_F = f(I_{F(AV)})$ per diode; sinusoidal current waveform where $a = \text{form factor} = I_{F(RMS)} / I_{F(AV)}$.




Fig.5. Typical junction capacitance per diode; $C_d = f(V_R)$; $f = 1$ MHz; $T_j = 25$ C to 125 C.




Fig.3. Typical and maximum forward characteristic $I_F = f(V_F)$; parameter T_j




Fig.6. Transient thermal impedance per diode; $Z_{th-j-hs} = f(t_p)$.

Rectifier diodes Schottky barrier

PBYR2045CTF, PBYR2045CTX series

MECHANICAL DATA

Dimensions in mm

Net Mass: 2 g




Fig.7. SOT186; The seating plane is electrically isolated from all terminals.

Notes

Notes

1. Refer to mounting instructions for F-pack envelopes.
2. Epoxy meets UL94 V0 at 1/8".

Rectifier diodes
Schottky barrier

PBYR2045CTF, PBYR2045CTX series

MECHANICAL DATA

Dimensions in mm

Net Mass: 2 g




Fig.8. SOT186A; The seating plane is electrically isolated from all terminals.

Notes

1. Refer to mounting instructions for F-pack envelopes.
2. Epoxy meets UL94 V0 at 1/8".

Rectifier diodes
Schottky barrier

PBYR2045CTF, PBYR2045CTX series

DEFINITIONS

Data sheet status	
Objective specification	This data sheet contains target or goal specifications for product development.
Preliminary specification	This data sheet contains preliminary data; supplementary data may be published later.
Product specification	This data sheet contains final product specifications.
Limiting values	
Limiting values are given in accordance with the Absolute Maximum Rating System (IEC 134). Stress above one or more of the limiting values may cause permanent damage to the device. These are stress ratings only and operation of the device at these or at any other conditions above those given in the Characteristics sections of this specification is not implied. Exposure to limiting values for extended periods may affect device reliability.	
Application information	
Where application information is given, it is advisory and does not form part of the specification.	
© Philips Electronics N.V. 1998	
All rights are reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner.	
The information presented in this document does not form part of any quotation or contract, it is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent or other industrial or intellectual property rights.	

LIFE SUPPORT APPLICATIONS

These products are not designed for use in life support appliances, devices or systems where malfunction of these products can be reasonably expected to result in personal injury. Philips customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Philips for any damages resulting from such improper use or sale.