

Screw Connectors for Printed Circuit Boards

974 (-DS) | 5.00 mm (0.197 in) Spacing - 2-26 poles

PICTURES



974-DS

TECHNICAL INFORMATION

Description

Can be installed anywhere on PCB without wires or screws interfering with the rest of PCB. Can be located next to each other back-to-back, front-to-front and front-to-back. The screws and wire entries are easily visible, accessible and usable, an ergonomic advantage.

Wire entrance at 45 angle to PC Board

Solid version

End-to-end stackable while maintaining the 5 mm spacing.

Technical Data

Center to Center Spacing: 5.000 mm (0.197 in)

Nominal Cross Section: 2.5 mm² (3875 mils²)

Wire Stripping Length: 6.500 mm (0.256 in)

Recommended Hole Diameter in PC Board: 1.300 mm (0.051 in)

Bill of Materials



Pole Version : 2-8
Molding : Polyamide, Self extinguishing UL 94, V-0
Color : Grey
Temperature limits :
 Short Time : 140°C (284°F)
 Continuous : 105°C (221°F)
 Low Limit : -40°C (-40°F)
Comparative Tracking Index : CTI ? 600 V
Oxygen Index Rating : 32 %

Pole Version : 9-26
Molding : Polyamide (glass fiber reinforced), Self extinguishing UL 94, V-0
Color : Grey
Temperature limits :
 Short Time : 200°C (392°F)
 Continuous : 105°C (221°F)
 Low Limit : -40°C (-40°F)
Oxygen Index Rating : 33 %

Terminal Body: Tin plated copper alloy
: Tin plated copper alloy
Screw: Slotted head, zinc plated clear passivated, steel substrate M3
Solder Pin: Tin plated copper alloy 1.0 mm (0.04 in.)

APPROVAL INFORMATION

UL File No. E69841 | CSA File No. LR24322

Type	Current (A)	Voltage (V)	Application Group	AWG	Screw Tightening Torque
 974 (-DS) 5.0 mm	20	300	B, D	26-12	4.5 lbfin
 974 (-DS) 5.0 mm	10	300	D, E	26-12	0.51 lbfin
	20	300	B	26-12	0.51 lbfin

UL: 24-26 AWG range for factory wiring only.

Alternative Approval Information


Type	Current (A)	Voltage (V)	Application Group	AWG	Screw Tightening Torque
974 (-DS)	10	300	D, E	26-12	0.51 lbfin
10.0 mm	20	300	B	26-12	0.51 lbfin

International Approval Information



Rated Impulse Withstand Voltage : 2500 V

TECHNICAL DRAWING



Description :

Length of Connector (L)

$L = \text{No. of Poles} \times \text{Center to Center}$

Spacing

SECTION A - SERIES 96 AND SERIES 97

Terminal Blocks for Printed Circuit Boards



Series 96 (inch spacing) and 97 (metric spacing) blocks have a higher profile than the Series 94 and 95 and provide larger clearance and creepage distances. This often provides a better current rating. The horizontal wire entry blocks have a raised base to allow the flow of flux and solvents during the soldering and cleaning phases of the soldering process.



These strips are available in solid 2-32 positions and can also be ordered in the dovetail version (-T) with 2 and 3 poles per block the dovetail system allows them to be assembled together in the needed combination to provide the designer with the needed number of positions while maintaining center-to-center pin-spacing. The dovetail system greatly reduces inventory needs and speeds up delivery. This series is provided with captive screws.



For the 9 to 32 pole version, molding are fiberglass-filled polyamide to provide longitudinal rigidity while maintaining the UL 94 V-0 rating this also allows higher process temperature limits.

These two series provide many versions and features that make them an excellent choice to overcome many design challenges and requirements.

Each product has a "How To Order" area as well as a complete listing of UL and CSA approval specifications, available options and accessories.