


**KEMET Part Number: PME261JC6100KR30**  
(P561CP104K500A)



Capacitor, film, 0.1 uF, +/-10% Tol, -40/+100C, General Purpose, 1000 VDC@85C, Lead Spacing=20.3 mm



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	24.00	MAX
H	16.50	MAX
T	11.30	MAX
S	20.30	+/-0.4
LL	30.00	+5
F	0.80	+/-0.05

Packaging Specifications	
Package Kind:	Bulk
Package Quantity:	150

General Information	
Supplier:	KEMET
Dielectric:	Metallized Paper
Application:	General Purpose
Sub Application:	DC or Low Frequency Pulse
Style:	Radial Molded
RoHS:	Yes

Specifications	
Capacitance:	0.1 uF
Voltage:	1000 VDC
Tolerance:	+/-10%
Voltage AC:	500 VAC
Rated Temperature:	85C
Temperature Range:	-40/+100C
Dissipation Factor @ 1 kHz:	1.3%
Insulation Resistance:	12 GOhm
Maximum dVdT:	950 v/us
Miscellaneous Electrical:	+70C temperature max. for AC operation

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.



© 2006-2014 IntelliData.net