

92mm sq.**San Ace 92L**

25mm thick





Model no. 109L0948C401 is not certified.

General Specifications

- Material Frame: Aluminum, Impeller: Plastics (Flammability: UL94V-1)
- Expected Life Refer to specifications (L10:Survival rate: 90% at 60°C , rated voltage, and continuously run in a free air state)
- Lead Wire ⊕red ⊖black or blue (Sensor) yellow
- Storage Temperature -30°C to +70°C (Non-condensing)

92×92×25mm [Mass : 170g]**Specifications** The following nos. **have pulse sensors.**

Model No.	Rated Voltage [V]	Operating Voltage Range [V]	Rated Current [A]	Rated Input [W]	Rated Speed [min ⁻¹]	Max. Air Flow [m ³ /min] [CFM]	Max. Static Pressure [Pa] [inchH ₂ O]	SPL [dB(A)]	Operating Temperature [°C]	Expected Life [h]
109L0912S401	12	10.2 to 13.8	0.32	3.84	3,500	1.69	59.7	66.6	- 20 to + 70	100,000
109L0912H401			0.21	2.52	2,850	1.38	48.7	45.1		
109L0912F401			0.14	1.68	2,450	1.18	41.7	32.3		
109L0912M401			0.11	1.32	2,100	1.01	35.7	23.5		
109L0912L401			0.08	0.96	1,700	0.80	28.2	16.7		
109L0924H401	24	20.4 to 27.6	0.12	2.88	2,850	1.38	48.7	45.1		
109L0924F401			0.08	1.92	2,450	1.18	41.7	32.3		
109L0924M401			0.06	1.44	2,100	1.01	35.7	23.5		
109L0924L401			0.05	1.2	1,700	0.80	28.2	16.7		
109L0948C401	48	43 to 53	0.1	4.8	3,400	1.65	58.3	64.2		80,000
109L0948H401		40.8 to 55.2	0.06	2.88	2,850	1.38	48.7	45.1		100,000

Available options: ⇒ **Without Sensor**Please inquire as the availability of these functions depend on the model. ⇒ **Lock Sensor** **Low speed Sensor****Dimensions (Unit : mm)****Reference dimension of mounting holes and vent opening (Unit : mm)**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Sanyo Denki:

[109L0912F402](#) [109L0912F4D01](#) [109L0912H402](#) [109L0912H4D01](#) [109L0912L402](#) [109L0912L4D01](#)
[109L0912M402](#) [109L0912M4D01](#) [109L0912S4D01](#) [109L0924F402](#) [109L0924F4D01](#) [109L0924H402](#)
[109L0924H4D01](#) [109L0924L402](#) [109L0924L4D01](#) [109L0924M402](#) [109L0924M4D01](#) [109L0948C4D01](#)
[109L0948H402](#) [109L0948H4D01](#)