

External-driven Piezo Transducer

TFM-33N




FEATURES:

- Low Frequency
- Low Current Drain
- Light and Compact


APPLICATIONS:

- Automatic Control Equipment
- Communication Equipment
- Electronic Instruments

DIMENSIONS: (Unit: mm)



CHARACTERISTICS:



ELECTRICAL SPECIFICATIONS :

Min. Sound Pressure Level at

3.0kHz/10V_{p-p} Square Wave/10cm 0dB(A)

Capacitance at 1000Hz 20nF 30 %

Allowable Input Voltage 30V P-P

Max. Consumption

at 3.0kHz/10V_{p-p} Square Wave 3mA

Resonant Frequency 3.0 0.5 kHz

Operating Temperature -20~+70℃

Case Material/Color PA6/Black

Weight 4.5g

PACKING INFORMATION:

Packing: 1800 pcs per export carton

Carton Size 5×27.5 cm

G. Weight: 10.5 kgs N. Weight: 9.0 kgs

Address: No. 12. Lane 722. Sangtian Road Jiangdong Science Garden

Ningbo, 315040 P. R. China

Fax No: (0574)87803761

Tel: (0574)87802511

