

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

ACTUATOR - SWITCH

CATALOG LISTING

JS-5

JS-5

M

DRAWING
NUMBER

ISSUE

1816

REPLACES

RELEASE NO. SR-1368

CHECK

REVISIONS

A	NEW DWG	C035725
D	B W	23 JUL 75
B	C038560	
J	A L	13 JUN 77
C	C047771	
	C J H	17 MAY 80
D	C079303	
	D L T	7 MAR 95

CHECK

25 JULY 75


DAW

75 CHECK


D B W23 JUL 75

FO-52848-A

DRAWN



.19 DIA X .12 WIDE OIL BRONZE ROLLER
(CONCENTRICITY .005 T. I. R.)



DOTTED LINES INDICATE
BASIC SWITCH IN PLACE


NOTE -



FURNISHED UNASSEMBLED

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS WITH ISMI SWITCH INSTALLED

OPERATING FORCE ----- 10 OZ MAX
RELEASE FORCE ----- 2 OZ MIN
PRETRAVEL ----- .078 MAX
DIFFERENTIAL TRAVEL ----- .015 MAX
OVERTRAVEL ----- .015 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR
REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

	DIM. mm	TOL. mm/in	DIM. in	TOL. mm/in
NO PLACES	X	1/.04	X	0.8/.03
ONE PLACE	X.X	0.4/.018	X.X	0.38/.015
TWO PLACES	X.XX	0.15/.006	X.XX	0.13/.005
THREE PLACES	X.XXX		X.XXX	
ANGLES				2°

DESIGN UNITS ☐ SI METRIC

☒ US CUSTOMARY

WEIGHT