


SBD Type : FCH30A10

OUTLINE DRAWING

FEATURES

- *TO-220AB Case
- *Fully Molded
- *Dual Diodes – Cathode Common
- *Low Forward Voltage Drop
- *High Surge Capability
- *Tj=150 °C operation



Maximum Ratings



Approx Net Weight: 1.75g

Rating	Symbol	FCH30A10			Unit
Repetitive Peak Reverse Voltage	V _{RRM}	100			V
Average Rectified Output Current	I _o	30	Tc=105°C	50 Hz Full Sine Wave Resistive Load	A
RMS Forward Current	I _{F(RMS)}	33.3			A
Surge Forward Current	I _{FSM}	250	50Hz Full Sine Wave ,1cycle Non-repetitive		A
Operating JunctionTemperature Range	T _{jw}	-40 to +150			°C
Storage Temperature Range	T _{stg}	-40 to +150			°C
Mounting torque	F _{tor}	recommended torque = 0.5			N•m


Electrical • Thermal Characteristics

Characteristics	Symbol	Conditions	Min.	Typ.	Max.	Unit
Peak Reverse Current	I_{RM}	$T_j= 25^{\circ}C, V_{RM}= V_{RRM}$ per arm	-	-	2	mA
Peak Forward Voltage	V_{FM}	$T_j= 25^{\circ}C, I_{FM}= 15 A$ per arm	-	-	0.88	V
Thermal Resistance	Rth(j-c)	Junction to Case	-	-	1.5	°C /W
	Rth(c-f)	Cace to Fin	-	-	1.5	°C /W


FCH_A_ OUTLINE DRAWING (Dimensions in mm)




Center Tap



FORWARD CURRENT VS. VOLTAGE



AVERAGE FORWARD POWER DISSIPATION





PEAK REVERSE CURRENT VS. PEAK REVERSE VOLTAGE

Tj= 150 °C




AVERAGE REVERSE POWER DISSIPATION






AVERAGE FORWARD CURRENT VS. CASE TEMPERATURE

$V_{RM} = 100V$



SURGE CURRENT RATINGS

$f = 50Hz$, Sine Wave, Non-Repetitive, No Load



JUNCTION CAPACITANCE VS. REVERSE VOLTAGE

$T_j=25^{\circ}\text{C}$, $V_m=20\text{mV}_{\text{RMS}}$, $f=100\text{kHz}$, Typical Value

FCH30A10 (per Arm)

