

BODY ZINC ALLO
NICKEL PLATED 70 MICROINCHES MIN



NICKEL PLATED 70 MICROINCHES MIN

CENTER CONTACT PHOSPHOR BRONZE
GOLD PLATED 10 MICROINCHES MIN



INSULATOR
POLYPROPYLENE (94V2)

BOARD LOCK PHOSPHOR BRONZE
TIN PLATED 200 MICROINCHES MIN



SOLDER TAIL COPPER OVER STEEL $\frac{2.54}{100}$
TIN PLATED 200 MICRINCHES MIN



RECOMMENDED MOUNTING HOLE
MAXIMUM PANEL THICKNESS: 5.40mm
RECOMMENDED MOUNTING TORQUE:
12 INCH-POUNDS MAX.



TOP VIEW



RECOMMENDED PCB HOLE CONFIGURATION

PART # 73101-0570

PS-73598-0051	PRODUCT SPECIFICATION
SPECIFICATION	DESCRIPTION

ENTER DESCRIPTION EC NO: URF2005-0098 DRAWN:CLLI CHKD: APPR: MUANG	2004/10/05 2004/10/06 2004/10/06	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM/IN		SCALE 1:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION
					mm	INCH	DRAWN BY CLLI	DATE 2004/06/30	TITLE 75 OHM BNC R/A PCB (DIE CAST) BNC-J/PCB BNC-PCB/RA/BK		
				4 PLACES	± ---	± ---	CHECKED BY	DATE			
				3 PLACES	± ---	± ---	PENNY	2004/06/30			
				2 PLACES	± 0.13	± ---	APPROVED BY	DATE	 MOLEX INCORPORATED		
				1 PLACE	± 0.25	± ---	MISEN	2004/06/30			
				ANGULAR ± 2 °		MATERIAL NO. 73101-0570		DOCUMENT NO. SD-73101-057		SHEET NO. 1 OF 1	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							